

SPI-10 FE 7 / 19 - Spring



3003019

<https://www.phoenixcontact.com/gb/products/3003019>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Spring, Push-in Spring

Your advantages

- Time saving push-in connection, tools not required
- Intuitive operation due to color-coded actuating push button
- Defined contact force ensures that contact remains stable over the long term

Commercial data

Item number	3003019
Packing unit	1,000 pc
Minimum order quantity	1,000 pc
Sales key	ACEPBC
Product key	ACEPBC
GTIN	4055626246994
Weight per piece (including packing)	1.37 g
Weight per piece (excluding packing)	1.37 g
Customs tariff number	73209090
Country of origin	DE

SPI-10 FE 7 / 19 - Spring

3003019

<https://www.phoenixcontact.com/gb/products/3003019>



Technical data

Notes

General	Further information and detailed dimensions are available in the download area.
---------	---

Product properties

Product type	Mounting material
Type	Push-in Spring

Connection data

Nominal cross section	10 mm ²
-----------------------	--------------------

Material specifications

Material (Spring contact)	Steel
---------------------------	-------

Classifications

ECLASS

ECLASS-13.0	27141190
-------------	----------

ETIM

ETIM 9.0	EC002848
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------