

Hexagon Bolts



Features

- No burrs and sharp edges
- Screw material: class 8.8 carbon steel, heat treat HRC 22-32
- Trivalent blue zinc / 3.8 µm min. finish
- Material and finish comply with 211/65/EU (RoHS)
- Meets DIN 933 standard

Length	L
3	2.8~3.2
4	3.76~4.24
5	4.76~5.24
6	5.76~6.24
8	7.71~8.29
10	9.71~10.29
12	11.65~12.35
14	13.65~14.35
16	15.65~16.35
20	19.58~20.42
25	24.58~25.42
30	29.58~30.42
35	34.5~35.5
40	39.5~40.5
45	44.5~45.5
50	49.5~50.5
55	54.4~55.6
60	59.4~60.6

[illegible]

Thread(6g)	S	K	E(Min)
M1.6x0.35	3.02~3.20	0.98~1.22	3.41
M2x0.4	3.82~4.00	1.28~1.52	4.32
M2.5x0.45	4.82~5.00	1.58~1.82	5.45
M3x0.5	5.32~5.50	1.88~2.12	6.01
M3.5x0.6	5.82~6.00	2.28~2.52	6.58
M4x0.7	6.78~7.00	2.68~2.92	7.66
M5x0.8	7.78~8.00	3.35~3.65	8.79
M6x1.0	9.78~10.00	3.85~4.15	11.05
M8x1.25	12.73~13.00	5.45~5.45	14.38
M10x1.5	16.73~17.00	6.22~6.56	18.90
M12x1.75	18.67~19.00	7.32~7.68	21.10
M16x2.0	23.67~24.00	9.82~10.18	26.75
M20x2.5	29.67~30.00	12.28~12.72	33.53

