

Features

- Tapered jaws for easier access.
- Jaws move in parallel throughout use.
- Smooth jaws to prevent damage to workpiece.
- Wire can be threaded down throat of plier.
- Jaws case hardened to HRC 57 for durability.
- Zinc-plated handles with detailing for added grip.

RS PRO Snipe Nose Smooth Jaws Parallel Plier, 125mm

RS Stock No.: 0606318



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Snipe Nose Smooth Jaws Parallel Plier

The parallel plier perfected for delicate working with small items or in restricted space. The pliers have a robust construction, with a rust resistant finish to ensure a long and dependable working life. Add the RS PRO smooth jaws snipe nose parallel plier to your toolbox. Engineered with smooth parallel jaws that taper for easier access. Perfect for working with high-shine aesthetic fixings and manipulating or straightening soft wire.

Benefits

- Easier access where space is confined.
- Ideal for holding, gripping and manipulating without damage.
- Parallel jaws grip securely along their whole length.
- Hold soft materials in a firm grip without marking.
- Manipulate, straighten and remove kinks in wire.
- Built to last, with a robust construction and rust-resistant finish.

Applications

A workbench essential, the snipe nose smooth jaws pliers (also known as chain nose pliers) are for use with soft metals and other delicate materials. Ideal for:

- Jewellery makers and horologists.
- Manufacturers of delicate and compact machinery.
- Model builders.

General Specifications

Plier Type	Snipe Nose Smooth Jaws Parallel Plier
Number of Pieces	1
Overall Length	125mm
Cutting Capacity	N/A
Material	Steel jaws, zinc-plated steel handles.
ESD Safe	No
Jaw Length	30 mm useable jaw length.
Jaw Opening	10mm
Non Sparking	No
Height Safe	No

Approvals

Declarations	REACH DoC
--------------	-----------

Similar Products

Stock No.	Brand	Product Name	Jaw Opening	Parallel	Overall Length
0606317	RS PRO	CENTRE CONDUCTOR CUTTING NIPPER	Up to 25 mm (Duct Rod Ø)	No	110 mm
0606320	RS PRO	Bullet & Snap Connector Insert Tool	46mm	No	145mm
0606319	RS PRO	Spanner Quick Grip	25 mm Max	No	135mm
0606316	RS PRO	Security Crimping and Cutter Plier	0.9mm (Ø cables)	No	212mm
0434623	RS PRO	Snipe Nose Serrated Jaws Parallel Plier	10mm	Yes	125mm
0606318	RS PRO	Snipe Nose Smooth Jaws Parallel Plier	10mm	Yes	125mm
0434621	RS PRO	Fine Nose Round Jaws Parallel Plier	11mm	Yes	125mm
0606312	RS PRO	Fine Clamping Plastic Jaws Parallel Plier	20mm	Yes	168mm
0434622	RS PRO	Flat Nose Nylon Jaws Parallel Plier	10mm	Yes	140mm
0441178	RS PRO	Side Cutter Parallel Plier for Hard Wire 125mm	10mm	Yes	125mm
0606314	RS PRO	Side Cutter Parallel Plier for Hard Wire 160mm	14mm	Yes	167mm
0606313	RS PRO	Side Cutter Parallel Plier for Hard Wire 140mm	8mm	Yes	140mm
0434617	RS PRO	Side Cutter Parallel Plier for Hard Wire 140mm, w/ Grip Handle	8mm	Yes	140mm

