

Rapid Classic Stapling Pliers K1

The world's bestselling pliers and the florist's favourite. Nice classic design with adjustable anvil for stapling and pinning. Perfect for the post room, shop, home and office.



Attributes

- Staples up to 50 sheets of paper (80 gsm)
- The world's bestselling pliers, attractive and classic design
- Adjustable anvil for stapling and pinning
- Traditional back loading functionality
- Available in 2 versions for Rapid staple No. 24 or 26, 6 mm - 8 mm
- 56 mm insertion depth
- 5 year guarantee when using Rapid staples



Specifications

Number	10510602
Colour	chrome
Material	Metal
Dimensions (W x H x D)	85 x 25 x 182 mm
Capacity of Stapling	5mm/50 sheets (80 gsm paper)
Integrated Staple Remover	No
Electrical	No
Type of Staples	Rapid 26/6-8+
Type of Stapling	Stapling, pinning
Insertion Depth	56mm
Loading Mechanism	Back loading
Package content	1
Weight	360 g
Pallet quantity	1800
Minimum order quantity	1800
EAN code	7313465106020