

Datasheet

RS Pro 11 W Oval Fluorescent Bulkhead light, IP65, Lamp Supplied

RS Stock No: **743-6471**



Product Details

RS Pro 11 W oval fluorescent bulkhead light has PC construction for added durability. This compact light has a pleasing appearance, which makes it to suit for both exterior and interior applications. The IP65 rated light uses a opal diffuser for an elegant output.

Features and Benefits

- Power of 11 W
- Oval shaped light
- IP65 rated

Specifications:

Case Material	PC
Depth	79 mm
Diameter	290 mm
Diffuser Colour	Clear
Diffuser Type	Opal
Dimensions	290 (dia.) x 79 mm
IP Rating	IP65
Lamp Shape	Round
Lamp Supplied	Yes
Lamp Type	Fluorescent
Shape	Oval
Type	Drum Lamp
Wattage	11 W
Base Colour	White
Life Hours	50000 h