

Portable Band Saw LXT®

DPB180

18V • 120 mm • 1.4 – 2,7 m/s

Compact band saw for spark-free cutting of metal

This light saw is easily portable and it is ideal for cutting pipes and fibre-reinforced hoses. Clean-edged and precise cutting. Cuts pipes of up to 120 mm, blade speed can be adjusted between 1.4 and 2,7 m/s. LED light and blade included.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Blade Diameter	13 x 0,5 x 1140 mm
Blade rapidity	1,4 - 2,7 m/s
Max. Cutting Capacity in Steel Pipe	120 x 120 mm
Sound Power Level (L _{WA})	92 dB(A)
Sound Pressure Level (L _{pA})	84 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Cutting metal	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Cutting metal	1,5 m/s ²
Product Dimensions (L x W x H):	523 x 231 x 313 mm
Tool weight with battery	6,8 - 7,1 kg
Vibration Level, Cutting Wood	≤ 2,5 m/s ²

User benefits

- Cutting metal quickly and without sparks.
- Large rubber tool rest protects work piece from scratches
- Electronic overload protection protects the user and the device
- Variable speed control dial enables user to match the speed to the application for greater versatility
- LED light illuminates the work site
- The rubber coating on the handle ensures a firm working grip
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing