



### Main

|                           |                                               |
|---------------------------|-----------------------------------------------|
| Range                     | Odace                                         |
| Product or component type | Wireless repeater                             |
| Device application        | Repeater                                      |
| Device mounting           | Flush                                         |
| Device presentation       | Mechanism with fixing frame and central plate |
| Colour tint               | Aluminium                                     |

### Complementary

|                                |                                                                                                                                                                                                                                                                                                                                     |
|--------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Communication port protocol    | IEEE 802.11 b/g/n                                                                                                                                                                                                                                                                                                                   |
| Transmission rate              | 300 Mbps (MCS15, 40 MHz)                                                                                                                                                                                                                                                                                                            |
| Network security encrypting    | WPA2-PSK                                                                                                                                                                                                                                                                                                                            |
| Actuator                       | Push-button                                                                                                                                                                                                                                                                                                                         |
| Switch application             | On/off switching                                                                                                                                                                                                                                                                                                                    |
| [Ue] rated operational voltage | 100...240 V                                                                                                                                                                                                                                                                                                                         |
| Control type                   | ON/OFF button                                                                                                                                                                                                                                                                                                                       |
| Integrated connection type     | Wi-Fi                                                                                                                                                                                                                                                                                                                               |
| Fixing mode                    | Clip-on support                                                                                                                                                                                                                                                                                                                     |
| Height                         | 45 mm                                                                                                                                                                                                                                                                                                                               |
| Width                          | 45 mm                                                                                                                                                                                                                                                                                                                               |
| Depth                          | 39 mm                                                                                                                                                                                                                                                                                                                               |
| Net weight                     | 0.53 kg                                                                                                                                                                                                                                                                                                                             |
| Market segment                 | Residential                                                                                                                                                                                                                                                                                                                         |
| Targeted channel               | Professional                                                                                                                                                                                                                                                                                                                        |
| Resistance to chemical agents  | Resistant to alcohol (70 %)<br>Resistant to alcohol (96 %)<br>Resistant to A-Lactic Acid<br>Resistant to diluted quaternary ammonium<br>Resistant to diluted bleach<br>Resistant to diluted ammonia<br>Resistant to soapy water<br>Resistant to crystal cleaner<br>Resistant to hydrogen peroxide 10 volumes<br>Resistant to hexane |

### Environment

|                                       |                   |
|---------------------------------------|-------------------|
| IP degree of protection               | IP20              |
| Standards                             | IEEE 802.11 b/g/n |
| Ambient air temperature for operation | -20...40 °C       |
| Ambient air temperature for storage   | -30...60 °C       |

## Offer Sustainability

|                            |                                               |
|----------------------------|-----------------------------------------------|
| Sustainable offer status   | Green Premium product                         |
| REACH Regulation           | <a href="#">REACH Declaration</a>             |
| REACH free of SVHC         | Yes                                           |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes                                           |
| Mercury free               | Yes                                           |
| Sustainable packaging      | Yes                                           |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |
| RoHS exemption information | <a href="#">Yes</a>                           |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a> |
| Circularity Profile        | <a href="#">End Of Life Information</a>       |