



6315DDU

Single-Row Deep Groove Ball Bearings

Parts Number

6315DDUC3

Boundary Dimensions

d	75	mm	Bore diameter
D	160	mm	Outside diameter
B	37	mm	Width
r (min.)	2.1	mm	Chamfer dimension

Basic Load Ratings

Cr	125000	N	Basic dynamic load rating
C0r	77000	N	Basic static load rating

Speeds

Grease	2800	min-1	Grease lubrication
--------	------	-------	--------------------

Abutment and Fillet Dimensions

da (min.)	86	mm	Diameter of shaft abutment
da (max.)	98.5	mm	Diameter of shaft abutment
Da (max.)	149	mm	Diameter of housing abutment
ra (max.)	2	mm	Radius of shaft or housing fillet
Dx (min.)	0	mm	Diameter of snap ring recess in the housing
Cy (max.)	0	mm	Distance from outer ring side face to snap ring back face

Calculation factors

fo	13.2		Factor
----	------	--	--------

Additional information

z	8		Number of Balls
Dw	26.988	mm	Ball Diameter

Mass

Mass approx.	3.08	kg	Mass approx.
--------------	------	----	--------------

