

Picture



Video & Audio

Image Sensor	1/3"CMOS Sensor
Video Resolution	UP To: 2560 x 1440 (4.0 Megapixels) at 15 frames/sec
Lens	f=2.8mm@F=1.6, f=8mm@F=1.6
Video Format	H.264,H.265
Field of View	Horizontal: 96°-38° Vertical: 55°-21°
Zoom Mode	6X hybrid zoom
Day & Night	IR-cut filter with auto-switching
Infrared Night Vision	Up to 15 Meters (50ft)(LED: 2pcs/850nm)
Color Night Vision	Spotlight: 1pcs/6500K/450 Lumens
Audio	Two-way Audio

Power

Battery	10400mAh rechargeable battery (Battery life varies based on settings, usage & temperature)
Solar	Reolink Solar Panel 2
DC Power	5V/2A

Interface

Power	USB Type-C port
System	Reset Button
Storage	MicroSD card slot (Max. 128GB)
Audio	Built-in Microphone and Speaker

Pan&Tilt

Pan &Tilt	Pan: 355°, Tilt: 0°~90°; (Speed can be set)
Preset	32
Auto Tracking	Support

Wi-Fi

Wireless Standard	IEEE 802.11a/b/g/n
Operating Frequency	2.4GHz/5GHz
Wireless Security	WPA-PSK/WPA2-PSK

Software Features

Frame Rate	Main Stream: 10fps - 15fps Sub Stream: 10fps - 15fps
Code Rate	Main Stream: 1024Kbps -4096Kbps Sub Stream: 64Kbps -512Kbps
OS Supported	PC: Windows, Mac OS; Smartphone: iOS, Android
Smart Alarm	PIR Detection/Human Detection/Vehicle Detection/Pet Detection
Record Mode	Motion Triggered Recording
Protocols & Standards	SSL, TCP/IP, UDP, UPNP, SMTP, NTP, P2P
Maximal User Access	Support up to 12 simultaneous video streams (10 substreams & 2 mainstreams)
Work with	Google Assistant, Reolink Cloud

Working Environment

Temperature	Operating Temperature: -10°C~+55°C (14°F~131°F)
Humidity	Operating Humidity: 20% ~ 85%
Waterproof	Support

Size & Weight

Dimension	228.2*147*129mm
Weight	1.4KG

Warranty

Limited Warranty	2-year limited warranty. For support, visit https://support.reolink.com/hc/en-us/
------------------	---

What's in the Box

- Reolink TrackMix WIFI
- Network cable - 1 m
- Power extension cable - 4.5 m
- Power adapter + battery, 64 GB microSD card, screws, waterproof lid, mounting template, surveillance sticker