

US-PML-P100 (D50) - Prohibition sign



1014217

<https://www.phoenixcontact.com/gb/products/1014217>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Prohibition sign, Card, red/white, pre-printed, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD: Diagonal bar, mounting type: adhesive, diameter: 50 mm, Number of individual labels: 4, text field height: 50 mm, text field width: 50 mm

Your advantages

- UniSheet - stick-on prohibition signs, color preprinted without symbol

Commercial data

Item number	1014217
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG2619
Product key	BG2619
Catalog page	Page 367 (C-3-2019)
GTIN	4046356786577
Weight per piece (including packing)	6.3 g
Weight per piece (excluding packing)	5.83 g
Customs tariff number	39203000
Country of origin	DE

US-PML-P100 (D50) - Prohibition sign



1014217

<https://www.phoenixcontact.com/gb/products/1014217>

Technical data

Product properties

Product type	Prohibition sign unprinted
Area of application	Prohibition signs
	Prohibition marking according to ISO 7010
Type	circular

Marking

Number of individual labels	4
Number of individual labels per row	2
Printing	Diagonal bar
Identification technology	Thermal transfer

Dimensions

Width	50 mm
Height	50 mm
Depth	0.09 mm
Diameter	50.00 mm
Min. material thickness	0.09 mm

Text field

Text field width	50 mm
Text field height	50 mm

Material specifications

Color	multicolored
	red (RAL 3001)
	white (RAL 9010)
Material	PVC
Components	Silicone-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 90 °C
Ambient temperature (assembly)	> 10 °C
Recommended ambient temperature (storage/transport)	22 °C
Recommended humidity (storage/transport)	50 % ... 55 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	2 years

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

US-PML-P100 (D50) - Prohibition sign



1014217

<https://www.phoenixcontact.com/gb/products/1014217>

Mounting type	adhesive
---------------	----------

US-PML-P100 (D50) - Prohibition sign



1014217

<https://www.phoenixcontact.com/gb/products/1014217>

Classifications

ECLASS

ECLASS-13.0	40200202
-------------	----------

ETIM

ETIM 9.0	EC001777
----------	----------

UNSPSC

UNSPSC 21.0	55121700
-------------	----------

US-PML-P100 (D50) - Prohibition sign



1014217

<https://www.phoenixcontact.com/gb/products/1014217>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk