

EM-CSS-FAN-35 - Fan



1276911

<https://www.phoenixcontact.com/in/products/1276911>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Replaceable fan for 35 mm wide CONTACTRON Speed Starters



Commercial data

Item number	1276911
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CK7
Product key	DK731Z
GTIN	4063151470845
Weight per piece (including packing)	43.1 g
Weight per piece (excluding packing)	43.1 g
Customs tariff number	84145915
Country of origin	TW

EM-CSS-FAN-35 - Fan

1276911

<https://www.phoenixcontact.com/in/products/1276911>



Technical data

Product properties

Product type	Fan
--------------	-----

EM-CSS-FAN-35 - Fan

1276911

<https://www.phoenixcontact.com/in/products/1276911>



Classifications

ECLASS

ECLASS-11.0	27371392
ECLASS-13.0	27371392
ECLASS-12.0	27371392

ETIM

ETIM 9.0	EC002498
----------	----------

UNSPSC

UNSPSC 21.0	39121100
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)

1276911

<https://www.phoenixcontact.com/in/products/1276911>

Mandatory accessories

CSS 0.25-1/3-EMC - Speed starter

1201520

<https://www.phoenixcontact.com/in/products/1201520>



Speed starter with soft start and configurable speed for starting and reversing motors up to 230 V AC and 0.25 kW, configurable motor protection, analog input, STO function up to SIL 3/PL e, single-phase load input, with integrated EMC filter

CSS 0.37-1/3-EMC - Speed starter

1201600

<https://www.phoenixcontact.com/in/products/1201600>



Speed starter with soft start and configurable speed for starting and reversing motors up to 230 V AC and 0.37 kW, configurable motor protection, analog input, STO function up to SIL 3/PL e, single-phase load input, with integrated EMC filter

EM-CSS-FAN-35 - Fan

1276911

<https://www.phoenixcontact.com/in/products/1276911>



CSS 0.25-3/3-EMC - Speed starter

1201713

<https://www.phoenixcontact.com/in/products/1201713>



Speed starter with soft start and configurable speed for starting and reversing motors up to 480 V AC and 0.25 kW, configurable motor protection, analog input, STO function up to SIL 3/PL e, three-phase load input, with integrated EMC filter

CSS 0.37-3/3-EMC - Speed starter

1201825

<https://www.phoenixcontact.com/in/products/1201825>



Speed starter with soft start and configurable speed for starting and reversing motors up to 480 V AC and 0.37 kW, configurable motor protection, analog input, STO function up to SIL 3/PL e, three-phase load input, with integrated EMC filter

EM-CSS-FAN-35 - Fan

1276911

<https://www.phoenixcontact.com/in/products/1276911>



CSS 0.55-3/3-EMC - Speed starter

1201828

<https://www.phoenixcontact.com/in/products/1201828>



Speed starter with soft start and configurable speed for starting and reversing motors up to 480 V AC and 0.55 kW, configurable motor protection, analog input, STO function up to SIL 3/PL e, three-phase load input, with integrated EMC filter

CSS 0.75-3/3-EMC - Speed starter

1201829

<https://www.phoenixcontact.com/in/products/1201829>



Speed starter with soft start and configurable speed for starting and reversing motors up to 480 V AC and 0.75 kW, configurable motor protection, analog input, STO function up to SIL 3/PL e, three-phase load input, with integrated EMC filter

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in