

FEATURES

- Excellent chemical resistance
- Available in black for discreet cable management or bundling
- Supplied in a pack of 10
- Using the non-releasable locking mechanism
- Made from high-quality PA66MP (Nylon 66) that offers high strength

RS PRO Black Nylon Cable Tray Cable Tie, 320mm x 7.6 mm

RS Stock No.: 233-196



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Introducing the RS PRO PA66 (Nylon) Cable Tray Tie, ideal for use with perforated cable trays. The self-locking mechanism ensures a secure hold when tying or fastening items together, while the ultra-durable nylon material provides a strong and long-lasting solution that can withstand harsh environments. In addition to this, the serrations on the cable tie surface provide a strong hold on bundles, even at high tension. These RS PRO cable ties are ideal for use when installing cabling in factories, industrial and manufacturing plants, as well as a wide range of other applications.

General Specifications

Type	Cable Tray
Colour	Black
Material	Nylon 66
Application	Automotive industry, Transportation, Aerospace Industry Oil and Gas industry, Cable management, Home/DIY
Minimum Operating Temperature	-45°C
Maximum Operating Temperature	85°C
Fire Behaviour	Flame Retardant
Quantity	100

Mechanical Specifications

Length	320mm
Width	7.6mm
Tensile Strength	539N

Approvals

Standards Met	UL 94 V-2
---------------	-----------



