



professionalLINE SteelCore Cable Reel IP44 33m H07BQ-F 3G1,5 *BE*

Basic data:

Product number: 9191334200
EAN: 4007123654567
Article type: SC 3114



Product information:

- Reel body made of steel plate, insulated front and back for heavy duty use.
- Innovative and ergonomic cable guide handle "cable pilot" for perfect cable-management during winding. Handle commutes on both sides and allows easy carrying and cable storage. For right and left handed easy to rewind.
- Large, sturdy fold-down turning handle rolls cables in and out effortlessly.
- Cold-resistant to -25 °C.
- Impervious to gasoline and oils.
- The BREMAXX®-PUR cable (BQ cable) is highly resistant to abrasions, crushing, UV light, cutting and tearing. In addition, it is acid-proof, oil-resistant, weatherproof and microbe-resistant. Remains highly flexible even at low temperature down to -40 °C.
- 4 water-jet protected earthed socket outlets with self-closing protective caps.
- With extra robust earthed plug.
- With thermal cut-out protection against overheating or overload.
- With visual readiness indicator in the socket insert.

Productline's value propositions:

Cable: H07BQ-F 3G1,5

Cable colour: orange

Colour: black, orange, grey

Cable diameter: 1.5 mm²

Cable length: 33m

Max. current carrying capacity – e: 16 A

Cable quality: Polyurethan PU

Degree of protection (IP): IP44

Number of sockets: 4

