

Datasheet

RS Pro Butt Wire Splice Connector, Red, Insulated, Tin Plated 22 → 16 AWG

RS Stock No: **534-288**



Product Details

RS Pro butt wire splice connector in red colour, is insulated and tin plated. This splice connector has a wire size of 22 to 16 AWG. It has a range of insulated crimp butt splice terminal made from copper with flared vinyl or nylon (mini-yellow) insulation. This insulated crimp butt splice wire connector is colour coded for use with different wire sizes including mini yellow 0.2 - 0.5 mm².

Features and Benefits

- Insulated crimp butt splice terminals made from copper with flared vinyl or nylon (mini-yellow) insulation
- This insulated crimp butt splice wire connectors are colour coded for use with different wire sizes
- Mini yellow 0.2 - 0.5 mm², red 0.5 - 1.0 mm², blue 1.5 - 2.5 mm² and yellow 2.5 - 6.5 mm²



ENGLISH

Specifications:

Colour	Red
Contact Material	Copper
Contact Plating	Tin
Insulation	Insulated
Insulation Material	PVC
Shrouded	Shrouded
Splice Type	Butt
Diameter	4 mm
Maximum Wire Size (AWG)	16 AWG
Maximum Wire Size (mm ²)	1.5 mm ²
Minimum Wire Size (AWG)	22 AWG
Minimum Wire Size (mm ²)	0.5 mm ²
Overall Length	24.5 mm
Wire Size	22 to 16 AWG
Current Rating	19 A
Temperature Rating	+75°C
Voltage Rating	600 V