

Features

- Maximum operating pressure is 50 bar.
- Operating temperature range -20°C to +100°C.
- Material: argely Stainless Steel with 17% chromium content
- ISO 6150-C

RS PRO Pneumatic Quick Connect Coupling

RS Stock No.: 0309299



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS PRO Series 107 Quick Connect Couplings Plugs


Pneumatic quick-connect coupling connectors are found across industry in pneumatic systems as diverse as robotic assembly lines and other equipment.

- Largely Stainless Steel with 17% chromium content.
- Maximum operating pressure is 50 bar.
- Operating temperature range -20°C to +100°C.
- Material: argely Stainless Steel with 17% chromium content
- ISO 6150-C

Specifications


Manufacturer Series	107
Coupling Type	Quick Connect Coupling Plug
Connection Standard	ISO 6150-C
Minimum Operating Temperature	-20°C
Maximum Operating Temperature	+100°C
Maximum Operating Pressure	50 bar
Flow Direction & Sealing	Through type coupling
Material	Stainless Steel
Finish	N/A
Connection Type	Hose Barb
Thread Size	N/A
Thread Standard	N/A
Thread Gender	N/A
Coupling Gender	Male
Threaded Connection	N/A
Seal material	N/A
Hose Barb Connection	10mm

Specifications



Dimensions (mm)		
SW	L	ØD
-	34	-

Pneumatic charts flow rate/Pressure drop from the single shut-off system
Pneumatische Durchflusswiderstandskurven mit einseitiger Absperrung (Druckluft)



Hydraulic charts flow rate/Pressure drop
Hydraulische Durchflusswiderstandskurve

