



3315RZ0-RA

Right Angle Light

The unique Peli™ 3315RZ0-RA (Right Angle) LED light is powered by a special designed lithium rechargeable battery that provides a life expectancy of over 2,000 cycles, 4 times more than the 500 cycles that batteries usually last. Lightweight and with three lighting modes (high/low/flashing), it shines up to 132 lumens of clear brilliant light and delivers a run time up to 34 hours in a small compact design. Additionally, this torch features a full time battery level indicator that is conveniently integrated into the switch. Its ergonomic polymer body is engineered with a sure-grip texture.

The 3315RZ0-RA (Right Angle) light is equipped with a right angle adapter with clip that provides hands free lighting. This adapter allows the torch head to articulate, directing the light exactly where you need it.

- Full Time Battery Level Indication
- Ingress Protected IPX7
- 3 modes High / Strobe / Low
- Lanyard (included)
- Special Lithium rechargeable battery provides 2,000 cycles (a 300% increase)
- Up to 132 Lumens
- Up to 34 hours, 15 minutes run time
- Articulating right angle adapter with clip (included)



DIMENSIONS

Length 8.27" (21 cm)

MATERIALS

Body Anti-static Impact Modified PC/PBT
O-Ring EPDM
Lens Anti-static coated Polycarbonate (PC)
Shroud Anti-static Impact Modified PC/PBT
Clip Stainless Steel

COLOURS

 High Visibility Yellow

LIGHT SPECS

Lamp Type LED

POWER

Battery Size 18650
Battery Type Lithium Iron Phosphate
Battery Quantity 1
Batteries Included yes
Rechargeable yes
Charge Time 10 hrs
Battery Level Indicator RGB LED
Volts 3.2v

WEIGHT

Weight With Batteries 6.2 oz (176 gr)
Weight Without Batteries 3.7 oz (105 gr)

SWITCH

Switch Type Push Button
Light Modes High / Low / Flashing

CERTIFICATIONS

Peli

c/ Provença, 388, Planta 7 • Barcelona, Spain 08025 • Phone: +34 934 674 999

info@peli.com • www.peli.com

ATEX Zone 0

IECEX ia

Document created on 02-19-19

OTHER

Minimum Pack

1

Package Code

C

FL1 STANDARD	HIGH	LOW
	132 LUMENS	15 LUMENS
	5h 0mins	34h 0mins
	108m	35m
	2931cd	308cd
	IP67	

ACCESSORIES