



ENGLISH

Datasheet

RS 2D Portable Task Light 38 W 110 V

Stock Number - 670-2759



Description

This range of Gripper Hand Lamps provide reliable portable lighting in areas such as garages, workshops, building sites, etc. by allowing the fitting to be clamped to an object

Features

- Robust construction
- 110V versions are colour coded yellow
- Pre fitted plug on Safety Grippers
- All Safety Grippers supplied with a polycarbonate guard, and are IP54 rated
- Standard Grippers supplied with an open wire guard
- Bayonet cap lampholder on all Grippers



ENGLISH

Range

230V Safety Gripper, 60W, 5m Cable, 16A Blue Plug	325-8375
110V Safety Gripper, 60W, 5m Cable, 16A Yellow Plug	325-8381
230V Safety Gripper, 60W, 5m Cable, 13A Plug	600-789
230V Standard Gripper, 100W	208-4296

Technical Specification

Voltage	110V ~ 50Hz 230V ~ 50Hz
IP Rating	IP54

Standards

- BS EN 60598 – 1
- BS EN 60598-2-8