


REVISIONS FOR DWG # FT1606

REV	CH.NO.	DESCRIPTION	DATE	REVISED BY
-	-	ORIGINAL DESIGN	06/10/16	ARON G



AWG	mm <sup>2</sup>	Barrel Length	Industry Standard	DIN Standard		L	L <sub>2</sub>	D	S	S <sub>2</sub>	A	B
2 x 16	2 x 1.5	8	FTI1608	FTD1608	2777.0	16	8	2.2000	0.1500	0.3000	6.5000	3.6000
2 x 16	2 x 1.5	12	FTI1612	FTD1612	2797.0	20	12	2.2000	0.1500	0.3000	6.5000	3.6000
2 x 16	2 x 1.5	18	FTI1618	FTD1618		26	18	2.2000	0.1500	0.3000	6.6000	3.6000
2 x 14	2 x 2.5	10	FTD1410		2778.0	19	10	2.8000	0.1500	0.4000	8	4.5000
2 x 14	2 x 2.5	12	FTD1412		2798.0	21	12	2.8000	0.1500	0.4000	8	4.5000
2 x 14	2 x 2.5	18	FTD1418			27	18	2.8000	0.1500	0.4000	8	4.5000
2 x 12	2 x 4	12	FTD1212		2799.0	22	12	3.5000	0.2000	0.5000	9	5.2000
2 x 12	2 x 4	18	FTD1218			28	18	3.5000	0.2000	0.5000	9	5.2000
2 x 10	2 x 6	12	FTI1012	FTD1012	2800.0	23	12	4.5000	0.2000	0.5000	11.4000	6.2000
2 x 10	2 x 6	18	FTI1018	FTD1018		29	18	4.5000	0.2000	0.5000	11.4000	6.2000
2 x 8	2 x 10	12	FTI0812	FTD0812	2801.0	24	12	5.8000	0.2000	0.5000	13.4000	7.6000
2 x 8	2 x 10	18	FTI1818	FTD1816		30	18	5.8000	0.2000	0.5000	13.4000	7.6000
2 x 6	2 x 16	16	FTI0616	FTD0616	2802.0	29	16	8.3000	0.3000	0.6000	17.2000	9.5000
2 x 6	2 x 16	25	FTI0625	FTD0625		38	25	8.3000	0.3000	0.6000	17.2000	9.5000

UNLESS OTHERWISE SPECIFIED  
 • ALL DIMENSIONS ARE IN MILLIMETERS  
 • THIRD ANGLE PROJECTION

• TOLERANCE	
XX	± 1.00 mm
XX.X	± 0.50 mm
XX.XX	± 0.20 mm
ALL	± XX mm

CIRTEK

This Drawing is the property of

**Altrech Corp.**

35 Royal Road  
 Flemington NJ 08822-6000  
 (908) 806-9400 • Fax (908) 806-9490

AND IS A CONFIDENTIAL DISCLOSURE  
 LENT WITHOUT CONSIDERATION OTHER  
 THAN THE BORROWER'S AGREEMENT  
 THAT IT SHALL NOT BE REPRODUCED,  
 COPIED, LENT, OR DISPOSED OF  
 DIRECTLY OR INDIRECTLY NOR USED  
 FOR ANY PURPOSE OTHER THAN THAT  
 FOR WHICH IT IS SPECIFICALLY  
 FURNISHED.

TITLE: Twin Insulated Wire Ferrules  
 2x16AWG to 2X06AWG

DRAWN BY: Aron Gyorgypal	06/08/16
CHECKED BY: Morgan E	06/08/16
RELEASED BY: Laszlo G	06/10/16

DRAWING NO.:	REV.:
M-Cad-6FU-FT1606	-
SCALE: -	SHEET: 1 OF: 1