

Tamper Resistant Hex and TORX[®] Tools







- Tools can be used to turn tamper resistant or standard fasteners
- Chamfered tool tips eliminate burrs and help tools seat in screw head
- Broad contact surface provides deep lobe
 engagement
- Straight, vertical sidewalls increase tool engagement and virtually eliminates camout
- · Precision machined for ease of use and superior fit



Bondhus Tamper Resistant Tools can be used to turn both tamper resistant and standard hex and TORX[®] fasteners.



Bondhus chamfers every Hex and TORX[®] tool we make. This process eliminates burrs and imperfections in the tool's tip that can prevent the tool from fitting properly or seating fully within the screw head.



Every Bondhus tool is designed and machined to achieve an optimal fit between tool and fastener. Tools insert quickly and easily into screw head and fit snug to generate greater torque and minimize slippage and stripping.

www.bondhus.com

If any Bondhus® tool breaks or fails to meet your expectations in any way, simply return it. We will replace it free of charge.



High Torque Steel:

Up to 20% stronger, with more torque and twice the wear resistance of standard grades of steel.

FINISH OPTIONS:



Corrosion-resistant finish:

Environmentally safe, provides better tool grip, resists solvents and is 5 times more corrosion resistant than competitor finishes.







Tamper Resistant Hex End L-Wrenches

Sets	PART#	MODEL#	PCS	LENGTH	CONTENTS	QTY	LIST
Inch	48332	HTR8	8	Long	3/32, 1/8, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"	1	
Metric	48386	HTR6M	6	Long	2.5, 3, 4, 5, 6, 8mm	1	

Single packed open stock for Tamper Resistant Hex End L-Wrenches are available in sizes listed above.







Tamper Resistant TORX® L-Wrenches

Sets	PART#	MODEL#	PCS	LENGTH	CONTENTS	QTY	LIST
TORX®	32432	TR-TL8S	8	Long	TR6, TR7, TR8, TR9, TR10, TR15, TR20, TR25	1	
IUKX®	32434	TR-TL8	8	Long	TR9, TR10, TR15, TR20, TR25, TR27, TR30, TR40	1	

Single packed open stock for Tamper Resistant Torx® L-Wrenches are available in Bulk and Tagged/Barcoded in sizes listed above.



Tamper Resistant GorillaGrip® TORX® Fold Ups

Sets	PART#	MODEL#	PCS	CONTENTS	QTY	LIST
TORX®	12636	TR-TF7S	7	TR7, TR8, TR9, TR10, TR15, TR20, TR25	1	
TURX	12638	TR-TF8	8	TR9, TR10, TR15, TR20, TR25, TR27, TR30, TR40	1	



Tamper Resistant TORX® Screwdrivers

Sets	PART#	MODEL#	PCS	CONTENTS	QTY	LIST
TORX®	33832	TR-SX8S	8	TR6, TR7, TR8, TR9, TR10, TR15, TR20, TR25	1	
TURX®	33834	TR-SX8	8	TR9, TR10, TR15, TR20, TR25, TR27, TR30, TR40	1	

Single packed open stock for Tamper Resistant Torx® Screwdrivers are available in sizes listed above.

Distributed by:

Bondhus Corporation

1400 E Broadway • PO Box 660 • Monticello, MN 55362 Tel: 763-295-2162 • Toll Free: 800-328-8310 • Fax: 763-295-4440

TORX® and TORX PLUS® are registered trademarks of Acument Intellectual Properties, LLC.

Bondhus, Protanium, ProGuard and GorillaGrip are trademarks of Bondhus Corporation.