

Previously known as: Versatouch® 72-286



Cut



Medium Duty

## Ergonomic industrial gloves offering excellent cut protection with comfort and durability

- **Advanced defenses:** HyFlex® 72-286 hand protection gloves are composed of Dyneema® material to deliver excellent cut protection
- **Improved durability:** These protective gloves are suitable for laundering up to 90°C, increasing their wear life
- **Enhanced ergonomics:** HyFlex® 72-286 work gloves feature an ergonomic design, which increases flexibility, dexterity and comfort
- **Food handling compliance:** These safety gloves are suitable for contact with all foodstuffs and come in three versions to better match the level of protection and dexterity required by specific applications



### Industries

- Food Processing

### Applications

- Primary cutting
- Assembly and disassembly of equipment

# HyFlex<sup>®</sup>

ADVANCED MECHANICAL PROTECTION

## 72-286

Exceptional cut resistance, comfort and durability

Previously known as: Versatouch<sup>®</sup> 72-286

### Key Features

- **Dyneema<sup>®</sup> material:** Excellent cut resistance assured
- **Suitable for laundering up to 90°C:** Extended wear life
- **Ergonomic design:** Ensuring enhanced wearer comfort

### Technologies



DMF free



### Performance Standards & Regulatory Compliance



EN388: 2016



2X4XD

### Specifications

| BRAND   STYLE              | DESCRIPTION                                                                                      | Gauge | SIZE           | LENGTH                         | PACKAGE                    |
|----------------------------|--------------------------------------------------------------------------------------------------|-------|----------------|--------------------------------|----------------------------|
| HyFlex <sup>®</sup> 72-286 | <b>Liner Material:</b> Dyneema <sup>®</sup> , Polyester, Spandex<br><b>Cuff Style:</b> Knitwrist | 10    | 6, 7, 8, 9, 10 | 260-330 mm; 10.23-13.99 inches | 3 pairs/bag, 2 bags/carton |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

Ansell, <sup>®</sup> and <sup>™</sup> are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

# Ansell