

## ToLEDo G9

ToLEDo RT G9 CL 470LM 827 SL

0028479



### Product features

- LED retrofit replacement for halogen mains voltage capsules
- ToLEDo Retro G9 has the same look and feel as halogen design thanks to glass construction body and wide light distribution
- Compact design
- Omni-directional light distribution
- 470lm = 40W halogen G9 lamp
- 90% energy saving
- A++ energy rating
- Non-dimmable
- Suitable for chandeliers, interior display, shop windows, decorative and general lighting applications



### PRODUCT OVERVIEW

IPC Code	0028479
Product name	ToLEDo RT G9 CL 470LM 827 SL
Technology	LED
Watt (Rated) (W)	3.5
Cap/Base	G9
Fixture rating	Open
General application	Hospitality, Residential & Consumer
ETIM Class	EC001959
E-number FI	4740824
Luminous flux (lm)	470
Colour temperature (K)	2700
Light colour	Homelight
CRI (Ra)	80
Wattage (W)	3.5
Product Voltage (V)	230

## ToLEDo G9

ToLEDo RT G9 CL 470LM 827 SL

0028479

Average life (Nominal) (h)	15000
Product EAN number	5410288284798

### DATA TABLE

#### General data

IPC Code	0028479
Product name	ToLEDo RT G9 CL 470LM 827 SL
Technology	LED
Watt (Rated) (W)	3.5
Cap/Base	G9
Fixture rating	Open
General application	Hospitality, Residential & Consumer
ETIM Class	EC001959
E-number FI	4740824

#### Optical data

Luminous flux (lm)	470
Luminous flux (Rated) (lm)	470
Colour temperature (K)	2700
Light colour	Homelight
CRI (Ra)	80
Lumen maintenance at end of nominal life (%)	70

#### Electrical data

Wattage (W)	3.5
Equivalent watt (W)	40
Starting time (max) (s)	0.5
Warm-up time to 60% of full light (max) (s)	1
Product Voltage (V)	230
Lamp power factor	0.8
No. Of switching cycles before premature failures	50000
Inrush Current (A)	0.8
Lamp Energy Label (class)	A++
kWh per 1000 hours burning time	4
Nominal Frequency (Hz)	50/60Hz
Max. Luminaires per 10A C Breaker	37
Max. Luminaires per 16A C Breaker	60
Max. Luminaires per 20A C Breaker	75

#### Lifetime data

Performance ambient temperature Tq (°C)	25
Average life (Nominal) (h)	15000
Average life (Rated) (h)	15000

## ToLEDo G9

ToLEDo RT G9 CL 470LM 827 SL

0028479

### Physical data

Nominal Product Length (mm)	59
Nominal Product Diameter (mm)	13
Weight (kg)	0.007

### Packaging

Single packaging type	Carton
Product EAN number	5410288284798
Packaging single length / height (cm)	2.0
Packaging single width (cm)	2.0
Packaging single depth (cm)	6.5
DUN14 (outer)	15410288284795
Units per outer package	10
Packaging outer length / height (cm)	15.5
Packaging outer width (cm)	6.5
Packaging outer depth (cm)	7.2

### Safety data

Breakage cleaning instructions	Not applicable
Special purpose lamp	No
Dry applications use only	kyllä
Suitable for household illumination	kyllä
Safety message	Not Suitable for totally enclosed fixtures

ToLEDo G9

ToLEDo RT G9 CL 470LM 827 SL

0028479

