

Main

Range of product	Harmony 9001K
Product or component type	Head for pilot light
Device short name	K

Complementary

Bezel material	Metal
Mounting diameter	30 mm
Cap/operator or lens colour	Without cap
Bulb base	BA 9s
Light block supply	Full voltage 24 V Full voltage 28 V
Shape of screw head	Round
Light source	Incandescent bulb
Operating mode	Normal
[Us] rated supply voltage	24...28 V
Light block supply	Full voltage
Size	30 mm

Environment

Product certifications	CSA LR25490 class 3211 03[RETURN]UL listed file E42259 CCN NKCR[RETURN]CE
NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins