



Product information

10 + 1 LED Rechargeable Mini Lamp HL 0400 A

Extremely small and handy, high light output.

- 10 super-bright Osram SMD LEDs on the front provide up to 6 hours of light ON time.
- Additional switching step for 1 SMD LED in the lamp head.
- On/off switch for front light (100 %, 50 %) and spotlight.
- Charging time about 4 hours.
- Rubber-clad housing.
- Integrated magnet on the rear.
- Integrated Li-Ion battery 3.6 V/2.6 Ah with charging indicator.
- USB charging interface, including USB charging cable.
- In blister packaging.

Technical information

Product number	1171590
EAN-Code	4007123654093
UP	1
Total luminous flux	400 lm
Power	5 W
Colour temperature	5700 K
Number of batteries	1 Pcs.
Battery type	Built-in battery pack
Battery technology	Lithium-Ion
Voltage	3.7 V
Battery capacity	2.6 Ah
Light duration max.	8 h
Charging time about	4 h
Degree of protection (IP)	IP40
Impact strength	Without
Protection class	I
Colour	black
Weight of product (without packaging)	0.28 kg
Length of product (without packaging)	3.10 cm

Width of product (without packaging) 2.40 cm

Height of product (without packaging) 26.20 cm

Weight of product (including packaging) 0.31 kg

Length of product (including packaging) 16.00 cm

Width of product (including packaging) 3.50 cm

Height of product (including packaging) 34.50 cm