1845 Automatic cable reel, with 3Gx2.5 mm² cable

CE IP42

Features:
- 3Gx2.5 mm² cable
- With thermal protection switch
- Cable length out of drum: 1 m (except for 1845 25-H07RN-F, 1.5 m)
- Supplied without incoming cable
- Rack mechanism can be disabled to keep cable pulled
- Max. power (rolled up): 2000W (230V-20°C)
- Max. power (unrolled): 3000W (230V-20°C)
- Supplied with a 180° swivel bracket and an additional quick connection bracket

	art.	Cavo	L m	Scocca	
018450365	1845 12-H05	H05VV-F	12+1	A	4,9 kg
018450367	1845 15-H07	H07RN-F	15+1	B	8,3 kg
018450377	1845 25-H07	H07RN-F	25+1,5	B	11 kg









