



DRAWING MADE IN AMERICAN PROJECTION

NUMBER C-163302





Ø20 MAX  
(0.5)



.695  
(17.7)

FOR Ø3 DR. PIN  
(2)



Ø12  
(0.3)

DIMENSIONS IN ( ) INCHES DO NOT SCALE PRINT

163302-8	PHOSPHOR BR.	PRE-TIN	▲
163302-7	PHOSPHOR BR.	NONE	▲
163302-6	BRASS	PRE-TIN	▲
163302-5	BRASS	NONE	▲
163302-4	PHOSPHOR BR.	PRE-TIN	
163302-3	PHOSPHOR BR.	NONE	
163302-2	BRASS	PRE-TIN	
163302-1	BRASS	NONE	
ORDER NO.	MATERIAL	PLATING	
DATE	DE	DATE	DATE
CHK	DATE	DATE	DATE

▲ = FOR USE ON MINIATURE APPLICATORS  
**CUSTOMER COPY FOR REFERENCE ONLY**

©1971 BY AMP-HOLLAND N.V. ALL RIGHTS RESERVED A-MP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.



WIRE RANGE	INSUL. RANGE	FIRST USED
10-25mm	100-500 DE	

SCALE	LOC	SIZE	NO	REV
4:1	H	A	C-163302	E

SOCKET mate-N-lok

AMP 1968