



Cut



Medium Duty

Medium-duty cut-resistant gloves, combining grip with abrasion and vibration resistance

- **Reinforced protection:** ActivArm® 97-003 safety gloves feature INTERCEPT™ Cut Resistance Technology, fused with Kevlar® and stainless steel fibers, for protective gloves that deliver ANSI A4/EN ISO D cut protection and six times greater laceration defenses than standard leather glove alternatives*
 - **Enhanced defenses and grip:** Gel padding reduces vibration and impacts, while nitrile foam coating makes for excellent grip in both wet and dry conditions
 - **Heightened comfort:** Designed with ZONZ™ Comfort Fit Technology, ActivArm® 97-003 safety work gloves boast an ergonomic, breathable design, equipped with adjustable Velcro® cuffs for increased dexterity
- *Based on an internal study comparing standard leather gloves with alternatives designed with ActivArm® liner and INTERCEPT™ Technology (3/11)



Industries

- Mining
- Oil and gas

Applications

- Positioning
- Operating of heavy machinery
- Scaffolding
- Hydraulic set and testing
- Crushing and unloading ore
- Primary grinding
- Hydraulic repair
- Product inspection
- Conveyer and longwall maintenance
- General pumping work
- Handling of tools
- Valve - line maintenance and repair
- Handling jagged metal
- Equipment maintenance Scaffolding Pipe handling and insulation Plumbing and sand blasting
- Heavy machine operation

Key Features

- **INTERCEPT™ Cut Resistance Technology:** ANSI/ISEA 105-2024 CUT A4 and EN ISO D resistance*
- **Gel padding:** For industrial gloves that reduce vibrations and impacts
- **ZONZ™ Comfort Fit Technology:** Enhanced fit, feel and wearer comfort
*6x greater than standard leather glove alternatives

Vulcanization Chemical Accelerators

- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



4X31D

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	PACKAGE
ActivArm® 97-003	Finishing: Palm Coated Coating Material: Foam Nitrile Liner Material: Nylon, Spandex, Stainless steel, Kevlar® Cuff Style: Velcro®	13	9, 10, 11	269-278 mm	12 pairs/carton

Technologies



INTERCEPT™
Cut Resistance Technology

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.