

CU CONNECTION NSX/CVS/INS 630 V.4P/ STAGED BUSBAR LINERGY BS

LVS04075

EAN Code: 3606481867360

Main

Range	PrismaSeT	
Range of product	PrismaSeT G	
Product or component type	Connection	
product name	PrismaSeT PrismaSeT G duct	
Accessory / separate part category	Current distribution accessory	
Standards	IEC 61439-2, inside enclosure IEC 61439-1, inside enclosure	
Product certifications	ASTA	

Complementary

Cubicle-device connection	Linergy BS busbar
installation description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm
Installed device	ComPact: fixed NSX400 without earth leakage protection - control: toggle vertical
	installation ComPact: fixed NSX400 without earth leakage protection - control: direct front rotary handle vertical installation
	ComPact: fixed NSX400 with earth leakage protection - control: toggle vertical installation
	EasyPact: fixed CVS400 without earth leakage protection - control: toggle vertical installation
	EasyPact: fixed CVS630 without earth leakage protection - control: toggle vertical installation
	EasyPact: fixed CVS400 without earth leakage protection - control: direct front rotary handle vertical installation
	EasyPact: fixed CVS630 without earth leakage protection - control: direct front rotary handle vertical installation
	EasyPact: fixed CVS400 with earth leakage protection - control: toggle vertical installation
	EasyPact: fixed CVS630 with earth leakage protection - control: toggle vertical installation
	ComPact: fixed NSX630 without earth leakage protection - control: toggle vertical installation
	ComPact: fixed NSX630 without earth leakage protection - control: direct front rotary handle vertical installation
	ComPact: fixed NSX630 with earth leakage protection - control: toggle vertical installation
	ComPact: fixed INS320400 - control: direct front rotary handle vertical installation
	ComPact: fixed INS500630 - control: direct front rotary handle vertical installation
	ComPact: fixed INV320400 - control: direct front rotary handle vertical installation
	ComPact: fixed INV500630 - control: direct front rotary handle vertical installation
[le] rated operational current	630 A
Product weight	2.28 kg
Quantity per set	Set of 1

1 Jul 2025 Life Is On Schneider

functional unit

- 300 mm PrismaSeT G floor-standing duct EasyPact CVS400 without fixed toggle vertical 3P 1 direct with long terminal shield 12
- 300 mm PrismaSeT G wall-mounted duct EasyPact CVS400 without fixed toggle vertical 3P 1 direct with long terminal shield 12
- 300 mm PrismaSeT G floor-standing duct EasyPact CVS400 without fixed toggle vertical 4P 1 direct with long terminal shield 12
- 300 mm PrismaSeT G wall-mounted duct EasyPact CVS400 without fixed toggle vertical 4P 1 direct with long terminal shield 12
- 300 mm PrismaSeT G floor-standing duct EasyPact CVS400 without fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12
- 300 mm PrismaSeT G wall-mounted duct EasyPact CVS400 without fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12 $\,$
- 300~mm PrismaSeT G floor-standing duct EasyPact CVS400 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12
- 300 mm PrismaSeT G wall-mounted duct EasyPact CVS400 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12
- 300 mm PrismaSeT G floor-standing duct EasyPact CVS630 without fixed toggle vertical 3P 1 direct with long terminal shield 12
- 300 mm PrismaSeT G wall-mounted duct EasyPact CVS630 without fixed toggle vertical 3P 1 direct with long terminal shield 12
- 300 mm PrismaSeT G floor-standing duct EasyPact CVS630 without fixed toggle vertical 4P 1 direct with long terminal shield 12
- 300 mm PrismaSeT G wall-mounted duct EasyPact CVS630 without fixed toggle vertical 4P 1 direct with long terminal shield 12
- 300 mm PrismaSeT G floor-standing duct EasyPact CVS630 without fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12
- 300 mm PrismaSeT G wall-mounted duct EasyPact CVS630 without fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12
- 300 mm PrismaSeT G floor-standing duct EasyPact CVS630 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12
- 300 mm PrismaSeT G wall-mounted duct EasyPact CVS630 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12
- 300 mm PrismaSeT G floor-standing duct ComPact INS320...400 fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 10
- 300 mm PrismaSeT G wall-mounted duct ComPact INS320...400 fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 10
- 300 mm PrismaSeT G floor-standing duct ComPact INS320...400 fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 10
- 300 mm PrismaSeT G wall-mounted duct ComPact INS320...400 fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 10
- 300 mm PrismaSeT G floor-standing duct ComPact INS500...630 fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12
- 300 mm PrismaSeT G wall-mounted duct ComPact INS500...630 fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12 $\,$
- 300 mm PrismaSeT G floor-standing duct ComPact INS500...630 fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12
- 300 mm PrismaSeT G wall-mounted duct ComPact INS500...630 fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12
- 300 mm PrismaSeT G floor-standing duct ComPact INV320...400 fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 10
- 300 mm PrismaSeT G wall-mounted duct ComPact INV320...400 fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 10 $\,$
- 300~mm PrismaSeT G floor-standing duct ComPact INV320...400 fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 10 $\,$
- 300 mm PrismaSeT G wall-mounted duct ComPact INV320...400 fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 10
- 300 mm PrismaSeT G floor-standing duct ComPact INV500...630 fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12
- 300~mm PrismaSeT G wall-mounted duct ComPact INV500...630 fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12
- 300 mm PrismaSeT G floor-standing duct ComPact INV500...630 fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12
- 300 mm PrismaSeT G wall-mounted duct ComPact INV500...630 fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12
- 300 mm PrismaSeT G floor-standing duct ComPact NSX400 without fixed toggle vertical 3P 1 direct with long terminal shield 12
- 300~mm PrismaSeT G wall-mounted duct ComPact NSX400 without fixed toggle vertical 3P 1 direct with long terminal shield 12
- 300 mm PrismaSeT G floor-standing duct ComPact NSX400 without fixed toggle vertical 4P 1 direct with long terminal shield 12
- 300 mm PrismaSeT G wall-mounted duct ComPact NSX400 without fixed toggle vertical 4P 1 direct with long terminal shield 12 300 mm PrismaSeT G floor-standing duct ComPact NSX400 without fixed direct front
- rotary handle vertical 3P 1 direct with long terminal shield 12 300 mm PrismaSeT G wall-mounted duct ComPact NSX400 without fixed direct front
- rotary handle vertical 3P 1 direct with long terminal shield 12 300 mm PrismaSeT G floor-standing duct ComPact NSX400 without fixed direct front
- rotary handle vertical 4P 1 direct with long terminal shield 12
- 300 mm PrismaSeT G wall-mounted duct ComPact NSX400 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12

300 mm PrismaSeT G floor-standing duct ComPact NSX630 without fixed toggle vertical 3P 1 direct with long terminal shield 12

300 mm PrismaSeT G wall-mounted duct ComPact NSX630 without fixed toggle vertical 3P 1 direct with long terminal shield 12

300 mm PrismaSeT G floor-standing duct ComPact NSX630 without fixed toggle vertical 4P 1 direct with long terminal shield 12

300 mm PrismaSeT G wall-mounted duct ComPact NSX630 without fixed toggle vertical 4P 1 direct with long terminal shield 12

300 mm PrismaSeT G floor-standing duct ComPact NSX630 without fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12

300 mm PrismaSeT G wall-mounted duct ComPact NSX630 without fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12

300 mm PrismaSeT G floor-standing duct ComPact NSX630 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12

300 mm PrismaSeT G wall-mounted duct ComPact NSX630 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12

300 mm PrismaSeT G floor-standing duct EasyPact CVS400 with fixed toggle vertical 3P 1 direct with long terminal shield 13

300 mm PrismaSeT G wall-mounted duct EasyPact CVS400 with fixed toggle vertical 3P 1 direct with long terminal shield 13

300 mm PrismaSeT G floor-standing duct EasyPact CVS400 with fixed toggle vertical 4P 1 direct with long terminal shield 13

300 mm PrismaSeT G wall-mounted duct EasyPact CVS400 with fixed toggle vertical 4P 1 direct with long terminal shield 13

300 mm PrismaSeT G floor-standing duct EasyPact CVS630 with fixed toggle vertical 3P 1 direct with long terminal shield 13

300~mm PrismaSeT G wall-mounted duct EasyPact CVS630 with fixed toggle vertical 3P 1 direct with long terminal shield 13

300 mm PrismaSeT G floor-standing duct EasyPact CVS630 with fixed toggle vertical 4P 1 direct with long terminal shield 13

300 mm PrismaSeT G wall-mounted duct EasyPact CVS630 with fixed toggle vertical 4P 1 direct with long terminal shield 13

300 mm PrismaSeT G floor-standing duct ComPact NSX400 with fixed toggle vertical 3P 1 direct with long terminal shield 14

300~mm PrismaSeT G wall-mounted duct ComPact NSX400 with fixed toggle vertical 3P 1 direct with long terminal shield 14 $\,$

300 mm PrismaSeT G floor-standing duct ComPact NSX400 with fixed toggle vertical

4P 1 direct with long terminal shield 14 300 mm PrismaSeT G wall-mounted duct ComPact NSX400 with fixed toggle vertical

4P 1 direct with long terminal shield 14 300 mm PrismaSeT G floor-standing duct ComPact NSX630 with fixed toggle vertical

3P 1 direct with long terminal shield 14
300 mm PrismaSeT G wall-mounted duct ComPact NSX630 with fixed toggle vertical

3P 1 direct with long terminal shield 14 $\,$ 300 mm PrismaSeT G floor-standing duct ComPact NSX630 with fixed toggle vertical

4P 1 direct with long terminal shield 14

300 mm PrismaSeT G wall-mounted duct ComPact NSX630 with fixed toggle vertical 4P 1 direct with long terminal shield 14

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	9.0 cm
Package 1 Length	29.0 cm
Package 1 Weight	2.238 kg
Unit Type of Package 2	P12
Number of Units in Package 2	36
Package 2 Height	21.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	92.5 kg

Logistical informations

Country of origin

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∅ Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better


Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration
Halogen content performance	Halogen free plastic parts product
PVC free	Yes
Silicon free	Yes

Use Again

○ Repack and remanufacture		
Circularity Profile	No need of specific recycling operations	
Take-back	No	

Technical Illustration

Dimensions



- All dimensions are approximate and are in Also see technical documentation.