

2160 PH 2

3C-Screwdriver

for cross-head screws PH

Code	ETIM
6683460	EC000144
EAN	UNSPSC
4010886803776	27-11-17-01
Country of origin	eCl@ss
Slovenia	21-04-04-01
Customs tariff number	
82054000	



Article description

- Acc. to DIN ISO 8764, tip according to DIN ISO 8764-1 PH
- 3-component Power-Grip³ handle with suspension hole
- Ergonomic handle shape for accurate, non-tiring work
- Positive-fit joint of handle and blade for optimum transmission of force
- Type of drive marked at the end of the handle
- Size 3 and 4 blade with hexagon bolster
- Blade of molybdenum-vanadium steel tempered

Article information

Contents (Qty of pieces)	1	Cap rotatable	no
Version/Execution	with hanging hole	Anti-magnetic	no
Net weight [kg]	0,119 kg	Ball head	no
Total length [mm]	210 mm	Handle available	yes
Total width [mm]	35 mm	Isolated	no
Total height [mm]	31 mm	Corrosion Protected	no
Material	Molybdenum-vanadium-Plus steel, tempered	Colour coding	yes
Blade length	100 mm	Unit-tested	no
Standard	DIN ISO 8764	Tip size cross recess (PH)	2
Low sparking design	no	Handle design	3C
Blade shape	Round	for screws of size	M3,5 - M5
Roll protection	no	Output tip reference standard	DIN ISO 8764-1 PH
Impact cap	no	Drive hexagon	no