



SIRIUS engineering Safety ES V1.0 Premium license key on USB flash drive software on CD floating license for one user engineering software class A 3 languages (de,en,fr) executable in: Windows 10 64-bit Professional/Enterprise Windows 7 32/64-bit SP 1 Professional/Ultimate/Enterprise reference hardware: SIRIUS MSS 3RK3 SIRIUS 3SK2 communication via system interface to PC (serial/USB) macro functionality content: set (1x DVD + 1x USB)

General technical data		
product designation		Safety ES V1.0
software version		V 1.0
product description		Engineering software for 3SK2 and 3RK3 safety relays; PREMIUM license; integrated graphic editor; integrated diagnostics and commissioning support; connection via PROFIBUS and system interface; license key on USB stick
national language of the software		german / english / french
product license		floating license for 1 user
software class		A
target system		SIRIUS MSS 3RK3, SIRIUS 3SK2
Features		
product component component library		No
<ul style="list-style-type: none"> • product function diagnostics function • product function controlled positioning • product function simulation function • product function technological function • product function analysis function • product function movement function • product function data acquisition function • product function commissioning function • product function communication function • product function project planning function • Product function maintenance function • product function evaluation function • product function parameterizing function 		<ul style="list-style-type: none"> Yes No No Yes No No No Yes Yes Yes No No Yes
Requirements		
processor clock frequency minimum	MHz	1 000
storage capacity		
<ul style="list-style-type: none"> • on hard disk required • of the main memory or RAM minimum 	Mbyte kbyte	280 1 024
design of the drive/storage medium required		
<ul style="list-style-type: none"> • CD-ROM • floppy disk • DVD drive 		Yes No No
Graphics card		
vertical image resolution of the graphics card	pixel	768
horizontal image resolution of the graphics card	pixel	1 024
number of colors of the graphics card		256

Software		
operating system required		Windows 7 SP1 64 Bit Ultimate / Professional / Enterprise (Standard installation); Windows 10 64 Bit Professional / Enterprise (Standard installation)
browser software required		no
viewer software required		no
Certificates/ approvals		
General Product Approval	other	

[Confirmation](#)

[Confirmation](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3ZS1316-6CC10-0YA5>

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3ZS1316-6CC10-0YA5>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3ZS1316-6CC10-0YA5>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3ZS1316-6CC10-0YA5&lang=en

last modified:

4/1/2025 