



Datasheet

ENGLISH

ECP-25 Euro series

25W plug-in power supply

Features



- Input Voltage: 90 – 264Vac
- Output Power: 25W
- No Load power consumption
- UK and European versions available
- Compact and light-weight plastic case
- Protections: short circuit/overload/ overheat
- 1 year warranty
- Dimensions: 80mm x 62mm x 50mm
- Connector: 2.1 x 5.5 x 9.5mm
- Weight: 220g

Part number	Voltage	Rated Current	Voltage range	Line Regulation	Load Regulation	Ripple and Noise	MTBF
726-2909	5V	5A	4.7 ~ 5.3V	± 1%	± 5%	<10%	100,000hrs min. MIL-HDBK – 217F (25°C)
726-2918	7.5V	3.3A	7.1 ~ 7.9V				
726-2911	9V	2.78A	8.5 ~ 9.5V				
726-2915	12V	2.08A	11.4 ~ 12.6V				
726-2924	15V	1.67A	14.25 ~ 15.75V				
726-2927	18V	1.39A	17.1 ~ 18.9V				
726-2921	24V	1.04A	22.8 ~ 25.2V				

Mechanical specification

