



Fuse-link, medium voltage, 71 A, AC 17.5 kV, 3", 76 x 292 mm, back-up, DIN, with striker

17.5AILSJ71

General specifications		
Product name		Eaton Busmann series medium voltage DIN fuse
Part no.		17.5AILSJ71
EAN		5027590437974
Product Length/Depth		326 millimetre
Product height		76 millimetre
Product width		76 millimetre
Product weight		3.3 kilogram
Compliances		VDE 0670-4 DIN 43625
Certifications		IEC60282-1
Product Tradename		None
Product Type		Medium voltage DIN fuse
Product Sub Type		None
Electrical data		
Amperage Rating		71 A
Voltage rating		17.5 kV
Breaking capacity		20 kA
Performance Cat According To IEC 60282-1		Back-up
Rated frequency - min		50 Hz
Class		Class back-up
Product specifications		
Application		indoor use transformer protection
Fuse indicator		With Striker
Standard		DIN

Technical data ETIM 9.0

Circuit breakers and fuses (EG000020) / Medium/high voltage fuse (EC003507)		
Electric engineering, automation, process control engineering / Electrical installation, device / Miniature circuit breaker system (MCB) / Medium-/high voltage fuse (ecl@ss13-27-14-19-11 [AGA534005])		
Rated current	A	71
Rated voltage	kV	17.5
Voltage type		AC
Rated frequency	Hz	50 - 50
Breaking capacity	kA	20
Utilization category		Other
Application		Primary side transformer protection
Length	mm	326
Diameter	mm	76
Performance category according to IEC 60282-1		Back-up
With striker		Yes
Standard		DIN
Release characteristic		Other
Installation technique		Air