

20021444-00010T1LF - Minitek127® :
1.27x1.27MM CTB, IDC RECEPTACLE, 10
POSITIONS



www.fci.com

Mating Half

- [20021511-00010T1LF](#)
- [20021512-00010T1LF](#)
- [20021521-00010T1LF](#)
- [20021611-00010T1LF](#)

Specifications

Approvals / Certifications	
Approvals / Certifications	UL APPROVED
Mechanical	
Durability (Mating cycles)	100 Cycles
Contact unmating force	20g Min./Pin
Mating force	220g Max./Pin
Dimensional	
Height (Pin)	3.45mm (0.136in).
Electrical	
Current rating	1A per contact
Resistance (Contact)	30m ohms Max. (After test 50 ohms Max.)
Resistance (Insulation)	100M ohms Min at 500 V DC/2 minute
Voltage rating	125V AC
General	
Gender	Female
Number of contacts (Total)	10
Series	20021444
Other Features	
Most Popular Configuration	Not Applicable
Packaging (Type)	Tube
Vacuum Pick-up Cap	No
Physical	
Plating (Contact area)	Gold Flash
Plating (Tail)	Gold Flash
Underplating (Contact)	40u" MIN Ni
Temperature (Range)	-40°C to +105°C