

101777

Wall Bracket 1-3 Products, 160 mm, Lime



Improve hygiene and extend equipment shelf-life with this add-on bracket. You can mix rubber clips and hooks, and easily remove the for cleaning. Rubber clips can hold products with diameters of 25–35 mm.

Technical Data

Item Number	101777
Holds products between	25 - 34 mm
Material	Polypropylene TPE Rubber
Complies with (EC) 1935/2004 on food contact materials¹	No
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Use of Phthalates	No
Box Quantity	5 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	1140 Pcs.
Quantity Per Layer (Pallet)	60 Pcs.
Box Length	330 mm
Box Width	175 mm
Box Height	95 mm
Length/Depth	160 mm
Width	80 mm
Height	60 mm
Gross Weight	0,2 kg
Net Weight	0,14 kg
Cubik metre	0,0008 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max usage temperature (non food contact)	80 °C
Min. usage temperature³	-10 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
Recycling Symbol "5", Polypropylene (PP)	Yes
GTIN-13 Number	5705022013575
GTIN-14 Number (Box quantity)	15705028013590
Commodity Code	39241000
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

3. Do not store the product below 0° Celsius.