



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2-1355587-3
AMP MODU II PIN HEADER 32 POS
ASSY



TE Part # 2-1355587-4
AMP MODU II PIN HEADER 32 POS
ASSY



TE Part # CAT-M8793-CH8172
MQS, CONNECTOR HOUSING



TE Part # 1-1355587-4
MOD2 PIN HEADER 32P



TE Part # CAT-SIGH262

Signal Header

Customers Also Bought

TE Part #1456987-1

2x4 Fem unsealed LP assy Key A

TE Part #2359943-2

96POS,MCON-1.2 CB,REC HSG,ASSY

TE Part #953122-4

40W MQS COVER ASSY (15d)

TE Part #2359941-6

96POS,MCON-1.2 CB,REC HSG,ASSY

TE Part #8-1564284-5

96POS,MCON-1.2 CB,REC HSG,ASSY

TE Part #CAT-M8793-CH8172

MQS, CONNECTOR HOUSING

TE Part #HD16-9-96SE

PLG, 9P, GRY, E, THRD, 16

TE Part #1418916-1

MULTI CORE CABLE APAPTER 180 DEGREE

TE Part #4-968972-1

MCP2,8 GEH ASSY 12P

Documents

Product Drawings

UMGEH M.SCHIEBER32P

English

CAD Files

Customer View Model

ENG_CVM_CVM_1355541-2_B.2d_dxf.zip

English

3D PDF



3D

Customer View Model

[ENG_CVM_CVM_1355541-2_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1355541-2_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

ZIELSETZUNG FUR LEISTUNGSDATEN TITLE: 32 MQS-5 PQ+2MQS BUCHSENGEHAUSE

English

Product Specification

English