

SPIRIT LEVEL MAGNETIC 300MM



- Magnets on the underside help fix the level to ferrous work pieces
- Crush proof, durable vials with high transparency for easy reading
- Highly resistant to ultra violet light and fluctuations in temperature
- Shock absorbent end protectors to reduce the risk of damage
- Temperature proof vial mountings to reduce the risk of distortion

Spirit Level 24x50mm Aluminium Magnetic 300mm

General information

Country of origin: Taiwan
Barcode: 5020385085206
Tarriff code Europe: 9015309000
ECCN US: EAR99
ETIM: EC000145
UNSPSC: 27111802

Attributes

Product type: Spirit Levels
Certificates: N/A
Tolerance: $\pm 0,75$ mm/m
Inverted tolerance: $\pm 0,75$ mm/m

Dimensions

Net weight (g): 330
Width (mm): 24
Height (mm): 50
Length: 300 mm

Technical changes and errors may occur. 01-08-2024 19:53



DESIGNED IN SWEDEN

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.



Sandbergsvägen 3
441 39 Alingsås, Sweden