

Features

- Crocodile Clips
- Automotive clip
- Jaw open 3/4" (19 mm) max
- Material: Zinc-Plated Steel
- Length: 3" (76.2 mm)
- Rating: 40 Amps

RS PRO Crocodile Clips, Zinc-Plated Steel Contact, 40A

RS Stock No.: 0205405



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Crocodile Clips



Product Description

- RS automotive alligator clips are designed for use within the automotive industry, the teeth mesh on three sides of the jaw ensuring a reliable contact and secure purchase, with screw and crimp termination, ideal for automotive analysers and test systems
 - RS Electric Heavy Duty, General Purpose, Crocodile and Alligator Clips
- A concise offering of steel and copper alligator and crocodile clips from RS suitable for applications including grounding clips, test meters clips, battery terminal connection and many others that require a durable and hardwearing alligator or crocodile clip

General Specifications

Material	Zinc-Plated Steel	
Product Name	Crocodile Clips	
Туре	Automotive Clip	
Insulated	No	
Connection Type	Can be attached by crimp or screw connection	

Commented [波辛1]:

Commented [波辛2]:

Electrical Specifications

Current rating

Dimensions (±10%)

Mechanical Specifications	
Jaw Opening (±10%)	3/4" (19 mm) max
Contact Material	Zinc-Plated Steel
Insulation Material	No
Dimensions (±10%)	Overall length 3"(76.2mm), overall width 13/20"(16.5mm), overall

height 15/16"(23.81mm)

40A


Approvals

Crocodile Clips



Standards Met	RoHS Compliant
Declarations	Reach

Spec Drawings Diameter



PRODUCT DIMENSION DRAWING AND ADDITIONAL INFORMATION