



Part Number : [1731110065](#)
Product Description : FCT Metal Backshell for D-Sub Connector, Shell Size 4, Straight Large Diameter Cable Outlet, Large Inner Chamber, with Rubber Bushing and #4-40 Locking Screws
Series Number : 173111
Status : Active
Product Category : D-Sub Backshells
Engineering Number : FMK4G-K201




Documents & Resources

Drawings
[1731110065_sd.pdf](#)

3D Models and Design Files
[1731110065_stp.zip](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 47; 34; 33
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	D-Sub Backshells
Series	173111
Description	FCT Metal Backshell for D-Sub Connector, Shell Size 4, Straight Large Diameter Cable Outlet, Large Inner Chamber, with Rubber Bushing and #4-40 Locking Screws
Magnetic	Yes
Product Name	FCT Products
Type	Rugged Metal
UPC	889056487658

Electrical

Shield Type	Solid Metal
Shielded	Yes

Physical

Cable Diameter	12.00-15.00mm
Material - Backshell	Zinc Die-cast
Material - Bushing	TPE
Material - Screw	Steel
Mounting Style	Locking Screw
Net Weight	97.300/g
Orientation	Straight
Packaging Type	Carton
Plating - Backshell	Nickel
Temperature Range - Operating	-35° to +100°C
Thread Size	4-40 UNC

Thread Type	Standard
Tightening Test Torque	40 Ncm
Waterproof / Dustproof	No

Use with Part(s)

Description	Part Number
Use With	FCT D-Sub, Size 4