

## Slim Line Compact keyboard G84-4400

with integrated trackball



### Key benefits

Cherry ML technology  
with Gold Crosspoint contacts

Small dimensions

Light weight

Integrated 16 mm Trackball plus 2 mouse keys

USB or PS/2 version

Color light grey or black

### Delivery volume

Keyboard, manual

### Technical data

#### Interface

USB or 2x PS/2 (keyboard, trackball)

#### Current input

USB: max. 100 mA  
PS/2: max. 32 mA (keyboard)  
typ. 5 mA (trackball)

#### Number of keys

83 = US and EU layout  
84 = European layouts

#### Cable length

approx. 1.75 m

#### Weight

approx. 563 g (without packaging)  
approx. 720 g (with packaging)

### Approvals

PS/2: CE, VDE/ÜG, cURus, FCC ID,  
VCCI Cl. 2, BSMI, C-Tick, RRL, GOST-R

USB: CE, VDE/ÜG, cURus, FCC DoC Cl. B,  
VCCI Cl. 2, C-Tick, GOST-R

### System requirements

PS/2: PS/2 connection for keyboard  
PS/2 connection for mouse (Trackball)

USB: USB connection & capable operating  
system (e.g. Windows 98, ME, 2000, XP)

### Guarantee period

2 years

### Dimensions

approx. 370 x 139 x 20 mm (keyboard)  
approx. 372 x 141 x 22 mm (packaging)

### Reliability

MCBF > 10<sup>9</sup> operations  
MTBF > 90.000 hours

### Storage temperature

-20 °C to 65 °C

### Operating temperature

0 °C to 50 °C

### Packaging unit

124 keyboards per master carton  
248 keyboards per pallet

## Order description

<b>Order number</b>	<b>Colour</b>	<b>Connection</b>
G84-4400LUBxx-0	light grey	USB
G84-4400PTBxx	black	USB
G84-4400LPBxx-0	light grey	2x PS/2
G84-4400PRBxx	black	2x PS/2

The xx in the order number defines the country version.

BE Belgium  
CH Switzerland  
DE Germany  
DK Denmark  
ES Spanish  
EU US English/ international with €  
FR France  
GB English (UK)  
IT Ital.  
NO Norway  
PO Portugal  
SF Sweden/Finland  
US US-English

Other country versions upon request.

Cherry GmbH  
Cherrystraße  
D-91275 Auerbach/Opf.  
Telefon: +49 9643 18-0  
Hotline: +49 9643 18-206  
Fax: +49 9643 18-1545  
Internet: [www.cherrycorp.com](http://www.cherrycorp.com)  
[www.cherry.de](http://www.cherry.de)

The manufacturer accepts no liability for errors or non-availability, and reserves the right to change specifications without prior notice.  
Technical data relate to product specifications only.  
Features may differ from those described. Only drawings combined with product specifications shall be deemed binding.

© 2004 Cherry GmbH