

####

87 05 250

KNIPEX Cobra®

#####

DIN ISO 8976

- #####
- #####
- #####
- #####
- ##### 61 HRC#####
- #####
- #####
- #####
- #####
- #####



####	87 05 250
EAN	4003773005681
#####	#####
###	#####
####	#####
##	366 g
##	250 x 50 x 18 mm
##	DIN ISO 8976
Reach	##
RohS	##
#####	
#####	25
#####	Ø 2
#####	46 mm
#####	Ø 50 mm
eCl@ss 5.1.4	21040301
ETIM 5.0	EC000164
ETIM 6.0	EC000164
proficl@ss 6.0	AAA936c004
UNSPSC 13.1	27112112

#####



