



MANUTAL black

Rubber-tyred wheels

STRONG POINTS

- ☛ Silent materials handling operations
- ☛ Resistance on uneven surfaces and to ageing
- ☛ Support wheel



APPLICATIONS

Mobile equipment and apparatus.



























Silent materials handling operations on uneven surfaces.

Excellent resistance to wear.

WHEEL RIM: black polypropylene copolymer.

TYRE: solid, black standard rubber with a trapezoidal profile.

HUB: symmetrical with plain bore or roller bearing.

								Code	EAN 13
80	35	40		12	80	0,140	5 080 1200	339680 500183 8	
		45		12	80	0,140	5 080 1245	339680 500180 7	
100	35	45		12	100	0,255	5 100 1200	339680 500184 5	
				12	100	0,295	5 100 1210	339680 500185 2	
125	35	45		12	125	0,425	5 525 1210	339680 500186 9	
				12	125	0,490	5 525 1260	339680 500187 6	
		60		20	150	0,485	5 125 1560	339680 500189 0	
160	41	45		12	150	0,675	1 160 1200	339680 500190 6	
				20	150	0,670	1 160 1220	339680 500191 3	
				12	150	0,705	1 160 1250	339680 500192 0	
	60		20	175	0,725	180 0020	339680 500193 7		
			20	175	0,785	180 0120	339680 700181 2		
200	50	60		20	200	1,260	181 0020	339680 500196 8	
				20	200	1,300	181 0120	339680 700184 3	
				25	200	1,380	181 0125	339680 700185 0	
250	50	60		20	250	1,960	182 0020	339680 500200 2	
				25	250	1,990	182 0025	339680 500202 6	
				20	250	2,065	182 0120	339680 500204 0	
				25	250	2,045	182 0125	339680 500206 4	