

CASES
1520
Case

Save as PDF



Peli protector cases - Cases for delicate instruments - 1520 case



Interior dimensions:
45.4 x 32.4 x 17.1 cm (18" x 13" x 7")

Watertight, crushproof, and dust proof

- Easy-open, double-step latches
- Open cell core with solid wall design - strong, light weight
- O-ring seal
- Automatic Pressure Equalization Valve
- Comfortable, rubber over-moulded handle
- Stainless steel hardware and padlock protectors
- Pick 'N' Pluck™ with convoluted lid foam
- Personalised nameplate service available
- Unconditionally Guaranteed



Black Silver Yellow Orange Desert_tan

Peli protector cases - Cases for delicate instruments - 1520 case SPECIFICATIONS

Exterior Dimensions (L x W x D)			Interior Dimensions (L x W x D)		
48.5 x 39.2 x 19.2 cm (19" x 15" x 8")			45.4 x 32.4 x 17.1 cm (18" x 13" x 7")		
Lid Depth	Bottom Depth	Total Depth			
4.6 cm (2")	12.5 cm (4.93")	17.1 cm (6.74")			
Lid Depth	Bottom Depth	Total Depth			
4.6 cm (1.81")	12.5 cm (4.93")	17.1 cm (6.74")			
Weight w/Foam	Weight w/o Foam	Buoyancy Max.			
4.24 kg. (9.35 lbs)	3.76kg (8.29 lbs.)	18.14 kg (40 lbs.)			
Range Temperature					
-40 / 99° C (-40 / 210° F)					

Personalized Nameplate Available

1520EU Case Certificates

- IP67(1 meter submersion for 30 minutes)
- MIL C-4150J
- Def Stan 81-41/STANAG 4280

Materials

Body	Latch	Lid O-Ring	Pins
Polypropylene	ABS	Polymer Stainless Steel	
Foam	Purge Body	Purge Vent	Purge O-Ring
1.3 lb Polyurethane	ABS	3 Micron Hydrophobic Non- Woven PET	70 Shore Nitrile

Configuration

Cat. #	Description
1520EU	Peli protector cases - Cases for delicate instruments - 1520 case

Peli protector cases - Cases for delicate instruments - 1520 case Accessories

Cat. #	Description