

1662AN

adjustable stylus dial indicator, reading to 0.01 mm

DIN 2270

- Centesimal reading
- Rotating dial
- 2 mm dia. carbide probe
- High-precision movement mounted on rubies
- Shank $\varnothing$ 8 mm
- C= Comparison range
- C= Dial field

	art.	C mm	B mm	D mm	G mm	 g
016620200	1662AN	0÷0,8	12	32	0,01	50

