

Metric Size - TU TU1208BU2-20

Datasheet

- Applicable tubing O.D.: Ø 2 to Ø 16 mm
- Operating temperature: -20 to 60 °C
- 29 colour variations.

Standard specifications

Size	1208 (O.D. Ø12, I.D. Ø8)
Color	BU2 (Clear Blue)
Roll Length	20 m
Reel Length	None
Suffix	None
-	Air, Water
Max. operating pressure at 20 °C	0.8 MPa
Weight	1.050 Kg

Additional information

Catalogue

[TU-29COLOR-A_EU.pdf](#)