

XCKT2102N12

Limit Switch , Steel Roller Plunger (ZCE02),
Conduit Entrance (0.5" NPT)



List Price \$96.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

Technical Characteristics

| | |
|-----------------------------|---------------------------------------|
| Actuation | Horizontal |
| Actuator Action | Momentary |
| Actuator | Steel Roller Plunger (ZCE02) |
| Head Type | Top Plunger |
| Operating Torque/Force | 106 Inch-Pounds (12Nm) |
| Repeat Accuracy | 0.1mm (on the tripping points) |
| Lever Arm Length | 30.5mm |
| Marketing Trade Name | OsiSense |
| Maximum Actuation Speed | 0.5 m/s |
| Roller Dimension | 11.6 x 3.5mm |
| RoHS | Yes |
| Type | XCKT |
| Type of Duty | General Duty |
| Body Type | Compact Modular (ZCT21) |
| Shock Resistance | 50G |
| Body Material | Plastic |
| Vibration Resistance | 25G |
| Connection Type | Conduit Entrance (0.5" NPT) |
| Weight | 0.231 lbs (0.105kg) |
| Contact Configuration | 1 N.O./1 N.C. |
| Contact Operation | Snap Action |
| Positive Opening | Yes |
| Terminal Type | Screw Clamp |
| Ampere Rating | 10A |
| Maximum Voltage Rating | 240VAC/250VDC |
| NEMA Enclosure Rating | NEMA 1/2/4/6/12/13 |
| Degree of Protection | IP66/67 |
| Approvals | UL Listed - CSA Certified - CE Marked |
| Operating Temperature Range | -13 to 158°F (-25 to 70°C) |
| Conforming to Standards | CENELEC EN 50047 |

Shipping and Ordering

Generated: 07/13/2010 16:00:24

| | |
|-------------------|---|
| Category | 22418 - Limit Switches, Medium Duty, Compact, IEC, Type XCKP & XCKT |
| Discount Schedule | T |
| GTIN | 00785901269618 |
| Package Quantity | 1 |
| Weight | 0.36 lbs. |
| Availability Code | Stock Item: This item is normally stocked in our distribution facility. |
| Returnability | Y |
| Country of Origin | MX |

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.