

Harmony 9001K Ø 30 metal pushbuttons



1



2

1 Pushbuttons, spring return

Type	Full guard		No guard		Extended guard	
Color			○	●	●	●
Contact	NO	NO + NC	NO	NO + NC	NO	NO + NC
Connection	Screw clamp terminals					
Complete product	9001KR1UH5	9001KR1UH13	9001KR3UH5	9001KR3UH13	9001KR2UH5	9001KR2UH13
Operator only	9001KR1U		9001KR3U		9001KR2U	
Contact block	9001KA2	9001KA1	9001KA2	9001KA1	9001KA2	9001KA1

2 Mushroom head pushbuttons

Type	Ø 40 trigger action Emergency stop pushbuttons	
Color	● Red	
Contact	NO + NC	2 NO + 2 NC
Connection	Screw clamp terminals	
Complete product	9001KR16H13	9001KR16H2
Operator only	9001KR16	9001KR16
Contact block	9001KA1	9001KA1



3



4

3 Pilot lights and illuminated pushbuttons

Type	Pilot lights with integral LED			Illuminated pushbuttons with integral LED			
Color	● Green	● Red	● Amber	● Green	● Red	● Amber	
Contact	-			NO + NC			
Connection	Screw clamp terminals						
Complete product	24 VAC/VDC	9001KP35LGG9	9001KP35LRR9	9001KP35LYA9	9001K2L35LGGH13	9001K2L35LRRH13	9001K2L35LYAH13
	48 VAC/VDC	9001KP36LGG9	9001KP36LRR9	9001KP36LYA9	9001K2L36LGGH13	9001K2L36LRRH13	9001K2L36LYAH13
	120 VAC/VDC	9001KP38LGG9	9001KP38LRR9	9001KP38LYA9	9001K2L38LGGH13	9001K2L38LRRH13	9001K2L38LYAH13
	220 VAC/VDC	9001KP7LGG9	9001KP7LRR9	9001KP7LYA9	9001K2L7LGGH13	9001K2L7LRRH13	9001K2L7LYAH13



5



6

5 Selector switches

Type	Black knob						
Positions	2 ∨ Stay put	2 ∨ Spring return from right	3 ∨ Stay put	3 ∨ Spring return left to center	3 ∨ Spring return both sides to center	4 ∨ Stay put	
Contact	2 NO + 2 NC						
Connection	Screw clamp terminals						
Complete operator	9001KS11BH2	9001KS34BH2	9001KS43BH2	9001KS46BH2	9001KS63BH2	9001KS53BH2	9001KS88BH2
Operator only	9001KS11B	9001KS34B	9001KS43B	9001KS46B	9001KS63B	9001KS53B	9001KS88B
Contact block	9001KA1						

6 Key switches

Type	Key (E10 key)					
Positions	2 ∨ Stay put	2 ∨ Spring return from right	3 ∨ Stay put	3 ∨ Spring return left to center	3 ∨ Spring return both sides to center	
Contact	2 NO + 2 NC					
Connection	Screw clamp terminals					
Complete operator	9001KS11K3H2	9001KS34K1H2	9001KS43K5H2	9001KS63K5H2	9001KS52K5H2	
Operator only	9001KS11K3	9001KS34K1	9001KS43K5	9001KS63K5	9001KS52K5	
Contact block	9001KA1					



7

7 Harmony 9001SK empty control stations with Ø 30 cut-outs for 9001K and 9001SK signaling units

Type	1 hole	2 holes	3 holes	4 holes	6 holes
Plastic control stations	9001SKY1	9001SKY2	9001SKY3	9001SKY4	9001SKY6
Die-cast control stations	9001KY1	9001KY2	9001KY3	9001KY4	9001KY6

Harmony 9001SK Ø 30 plastic pushbuttons



1 Pushbuttons, spring return

Type	Full guard		No guard				Extended guard	
Color			○ ● ● ● ● ● ●	Set of 7 clip-in colored caps				
Contact	NO	NO + NC	NO	NO + NC	NO	NO + NC	NO	NO + NC
Connection	Screw clamp terminals							
Complete product	9001SKR1UH5	9001SKR1UH13	9001SKR3UH5	9001SKR3UH13	9001SKR2UH5	9001SKR2UH13		
Operator only	9001SKR1U		9001SKR3U				9001SKR2U	
Contact block	9001KA2	9001KA1	9001KA2	9001KA1	9001KA2	9001KA1		

2 Mushroom head pushbuttons

Type	Ø 40 trigger action Emergency stop pushbuttons	
Color	● Red	
Contact	NO + NC	2 NO + 2 NC
Connection	Screw clamp terminals	
Complete product	9001SKR16H13	9001SKR16H2
Operator only	9001SKR16	9001SKR16
Contact block	9001KA1	9001KA1



3 Pilot lights and illuminated pushbuttons

Type	Pilot lights with integral LED			Illuminated pushbuttons with integral LED			
Color	● Green	● Red	● Amber	● Green	● Red	● Amber	
Contact	-			NO + NC			
Connection	Screw clamp terminals						
Complete product	24 VAC/VDC	9001SKP35LGG9	9001SKP35LRR9	9001SKP35LYA9	9001SK2L35LGGH13	9001SK2L35LRRH13	9001SK2L35LYAH13
	48 VAC/VDC	9001SKP36LGG9	9001SKP36LRR9	9001SKP36LYA9	9001SK2L36LGGH13	9001SK2L36LRRH13	9001SK2L36LYAH13
	120 VAC/VDC	9001SKP38LGG9	9001SKP38LRR9	9001SKP38LYA9	9001SK2L38LGGH13	9001SK2L38LRRH13	9001SK2L38LYAH13
	220 VAC/VDC	9001SKP7LGG9	9001SKP7LRR9	9001SKP7LYA9	9001SK2L7LGGH13	9001SK2L7LRRH13	9001SK2L7LYAH13



5 Selector switches

Type	Black knob						
Positions	2 ∨ Stay put	2 ∇ Spring return from right	3 ∨ Stay put	3 ∇ Spring return left to center	3 ∇ Spring return both sides to center	4 ∨ Stay put	
Contact	2 NO + 2 NC						
Connection	Screw clamp terminals						
Complete operator	9001SKS11BH2	9001SKS34BH2	9001SKS43BH2	9001SKS46BH2	9001SKS63BH2	9001SKS53BH2	9001SKS88BH2
Operator only	9001SKS11B	9001SKS34B	9001SKS43B	9001SKS46B	9001SKS63B	9001SKS53B	9001SKS88B
Contact block	9001KA1						



Contact blocks, legend plates, and other accessories for Ø 30 devices

Contact	NO + NC	NO	NC	NO + NC (Reed)	NO (Reed)
Contact blocks	9001KA1	9001KA2	9001KA3	9001KA51	9001KA52
Legend marking	Unmarked			Marked	
Legend color	Black	Red	White text on black (1) or red (2) background		Black text on yellow background
Aluminium legend plates for metal range	9001KN200	9001KN200R	ON (1)	9001KN203	EMERGENCY STOP (ext. Ø 60 mm) 9001KN9330
	9001KN300 (large)	9001KN300R (large)	OFF (2)	9001KN204	EMERGENCY STOP (ext. Ø 90 mm) 9001KN8330
			EMERGENCY STOP (2)	9001KN205	
Standard clear rubber boot	For pushbutton head 9001KR●U		9001KU7		
Joystick controller	Spring return, 5 positions only		9001K35		