

CZL185-10HRA



CU 45DEGREE LUG 185SQMM M10



General Information

Extended Product Type	CZL185-10HRA
Product ID	7TBH007940R0378
EAN	5415022378955
Catalog Description	CU 45DEGREE LUG 185SQMM M10
Long Description	Copper One-Hole 45 Degree Angle Metric Lug, Standard Barrel, Cable Size 185mm ² , Stud Size M10, Length 60.1mm, Flat 30.5mm, Hole Spacing 16mm

Ordering

EAN	5415022378955
Minimum Order Quantity	400 piece
Customs Tariff Number	8536904000

Dimensions

Product Net Weight	138.352 g
--------------------	-----------

Container Information

Package Level 1 Width	199.898 mm
Package Level 1 Height	102.108 mm
Package Level 1 Depth / Length	72.898 mm
Package Level 2 Units	400 piece
Package Level 2 Width	320.04 mm
Package Level 2 Height	220.98 mm
Package Level 2 Depth / Length	215.9 mm
Package Level 3 Units	400 piece

Additional Information

Brand / Label	Spec-Kon
Insulation Material	None
Material	Copper
Product Main Type	COMPRESSION CONNECTORS
Product Name	COPPER LUG
Product Type	Copper One-Hole 45 Degree Metric Lug

UPC

786210083926

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	CZL185-10HRA
Instructions and Manuals	CZL185-10HRA

Classifications

ETIM 6	EC001051 - Tube cable lug for copper conductors
UNSPSC	39121405
WEEE Category	Product Not in WEEE Scope

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors

