



## Main

Range	Acti 9
Product name	Acti 9 SBI
Product or component type	Fuse-disconnector
Device short name	SBI
Poles description	2P

## Complementary

[In] rated current	32 A 40 A 50 A 63 A 80 A 100 A 125 A
Fuse curve	AM GG
Fuse size	22 x 58 mm
[Ue] rated operational voltage	690 V AC
Mounting support	35 mm symmetrical DIN rail
9 mm pitches	8
Connections - terminals	Screw clamp terminals1 cable(s) 2.5...25 mm <sup>2</sup> rigid Screw clamp terminals1 cable(s) 2.5...25 mm <sup>2</sup> flexible
Tightening torque	3.5 N.m

## Environment

Standards	IEC EN 60947-3
Pollution degree	3
Ambient air temperature for operation	-20...60 °C
Ambient air temperature for storage	-40...80 °C

## Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Number of Units in Package 1	1
Package 1 Weight	369 g
Package 1 Height	7 cm
Package 1 width	7.6 cm
Package 1 Length	12.7 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	3
Package 2 Weight	1.195 kg
Package 2 Height	8 cm
Package 2 width	13 cm
Package 2 Length	22 cm
Unit Type of Package 3	S03
Number of Units in Package 3	27
Package 3 Weight	11.043 kg
Package 3 Height	30 cm
Package 3 width	30 cm
Package 3 Length	40 cm

## Offer Sustainability

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------