



## NT 70/2

Powerful wet/dry vacuum cleaner with 70 l container capacity and up to three motors.

### 1 Integrated accessory storage

- Large bumper with accessory storage.

### 3 Ergonomic push handle

- The NT 70 has an ergonomic push handle so that the machine can be rolled.

### 2 Integrated drain hose

- The container is easy to empty via the drain hose. Extremely practical due to the very large 70 litre container capacity.

### 4 Robust bumper

- The robust bumper protects the machine from knocks and bumps.



## NT 70/2

- Robust bumper, large wheels
- Ergonomic push handle
- Optional wet filter available

### Technical data

Order No.	1.667-277.0	
EAN code	4039784725447	
Air flow rate	l/s	2 x 56
Vacuum	mbar / kPa	254 / 25.4
Container capacity	l	70
Max. rated input power	W	2400
Standard nominal width		40
Sound pressure level	dB(A)	75
Container material		plastic
Number of motors		2
Frequency	Hz	50-60
Voltage	V	220-240
Weight	kg	24.9
Dimensions (L x W x H)	mm	510 x 740 x 1010

### Equipment

Suction hose	m	4
Suction tube, metal 2 x 0.5 m		■
Filter bag		Paper
Wet and dry floor nozzle	mm	400
Crevice nozzle		■
Cartridge filter		■
Cartridge filter		Paper

■ Included in delivery.

# ACCESSORIES FOR NT 70/2

## 1.667-277.0

**KÄRCHER**


		Order No.	Quantity	ID	Length	Width	Price	Description	
<b>Cartridge filter paper</b>									
Cartridge filter, paper	1	6.907-038.0	1 piece(s)					Paper cartridge filter (M BIA-C dust class M), suitable as a main filter for dry and wet pick up.	■
<b>Floor nozzles</b>									
Multi-purpose nozzle, wet/dry	2	6.906-554.0	1 piece(s)	ID 40		360 mm		All-purpose plastic nozzle (DN 40) with 360 mm working width. With side rollers, brush strips (6.905-878.0) and squeegees (6.905-877.0). Only for NT vacuum cleaners.	■
Wet and dry floor nozzle	3	2.889-117.0	1 piece(s)	ID 40		400 mm		The wet and dry floor nozzle (DN 40) allows quick changing of the squeegees/brush and is ideal for wet vacuum cleaning of large areas.	■
	4	6.907-510.0	1 piece(s)	ID 40		400 mm			■
Multi-purpose nozzle, wet/dry	5	6.903-018.0	1 piece(s)	ID 40		370 mm		All-purpose aluminium nozzle with 370 mm working width. With height-adjustable side rollers, brush strips (6.903-064.0) and oil-resistant squeegees (6.903-081.0). Only for NT vacuum cleaners.	□
	6	6.906-383.0	1 piece(s)	ID 40		450 mm		All-purpose aluminium nozzle (DN 40) with 450 mm working width. With height-adjustable side rollers, brush strips (6.903-065.0) and oil-resistant squeegees (6.906-146.0). Only for NT vacuum cleaners.	□
	7	6.906-384.0	1 piece(s)	ID 35		370 mm		All-purpose aluminium nozzle (DN 35) with 370 mm working width. With height-adjustable side rollers, brush strips (6.903-064.0) and oil-resistant squeegees (6.903-081.0). Only for NT vacuum cleaners.	□
	8	6.906-513.0	1 piece(s)	ID 35		360 mm		All-purpose plastic nozzle (DN 35) with 360 mm working width. With side rollers, brush strips (6.905-878.0) and squeegees (6.905-877.0). Only for NT vacuum cleaners.	□
<b>Crevice nozzles</b>									
Crevice nozzle	9	6.903-033.0	1 piece(s)	ID 40	290 mm			Plastic crevice tool (DN 40) for vacuuming in crevices and corners. Length: 290 mm.	■
	10	6.900-385.0	1 piece(s)	ID 35	210 mm			Plastic crevice tool (DN 35) for vacuuming in crevices and corners. Length: 210 mm.	□
	11	6.900-922.0	1 piece(s)	ID 35	500 mm			Plastic crevice tool (DN 35) for vacuuming in crevices and corners. Length: 370 mm.	□
	12	6.905-817.0	1 piece(s)	ID 40	400 mm			Metal crevice tool (DN 40) for vacuuming in crevices and corners. Length: 400 mm.	□
<b>Suction tubes, metal</b>									
Suction tube	13	6.900-275.0	1 piece(s)	ID 40	0.5 m			Chromium-plated metal suction tube (DN 40, 1x0.5 m), standard for virtually all two-motor industrial vacuum cleaners. Optional for industrial single-motor NT vacuum cleaners with DN 40 suction hose.	■
	14	6.900-514.0	1 piece(s)	ID 35	0.5 m			Chromium-plated metal suction tube (DN 35, 1x0.5 m), standard for virtually all single-motor industrial NT vacuum cleaners.	□
<b>Complete suction hoses (clip system)</b>									
Suction hose	15	4.440-678.0	1 piece(s)	ID 40	4 m			4 m electrically non-conductive suction hose with bend, bayonet at vacuum end and C 40 clip connection at accessory end. Without module.	■
Suction hose + ID 40 bushing	16	4.440-784.0	1 piece(s)	ID 40	16 m			16 m suction hose (C-DN 40) with bayonet and straight adapter.	□
<b>Fabric filter</b>									
Membrane filter	17	6.904-282.0	1 piece(s)					Polyester needle fleece membrane/fabric filter - BIA-C -, washable up to 40°C, metal fibres for earthing. Suitable for virtually all industrial two-motor NT vacuum cleaners.	□

■ Included in delivery. □ Available accessories.

# ACCESSORIES FOR NT 70/2

## 1.667-277.0

**KÄRCHER**


		Order No.	Quantity	ID	Length	Width	Price	Description	
<b>Paper filter bags (two-ply)</b>									
Paper filter bags	18	6.904-285.0	5 piece(s)					5 3-ply, tear-resistant paper filter bags. BIA-(U, S, G, C) dust class M. For all NT 48/1, NT 65/2 Eco + Me and NT 72/2 Eco Tc models.	<input type="checkbox"/>
<b>Plastic sacks for dust-free disposal</b>									
Plastic sack for dust-free disposal	19	6.900-698.0	10 piece(s)					PE plastic sack.	<input type="checkbox"/>
<b>Wet filter bag</b>									
Wet filter bag	20	6.904-252.0	5 piece(s)					Approved for dust class L, general cleaning, wet and dry, tear-resistant.	<input type="checkbox"/>
<b>Bends, stainless steel</b>									
Bend, stainless steel, ID 35	21	6.903-141.0	1 piece(s)	ID 35				Stainless steel and crooked, ID 35	<input type="checkbox"/>
Bend, stainless steel, ID 40	22	6.902-079.0	1 piece(s)	ID 40				Stainless steel and crooked, ID 40	<input type="checkbox"/>
<b>Bend, plastic</b>									
Plastic bend	23	5.031-718.0	1 piece(s)	ID 35				Plastic bend (DN 35) with C-35 clip system. For all industrial single-motor NT 361 to NT 611 Eco models (except NT Eco M and NT Eco H).	<input type="checkbox"/>
Bend, plastic, electrically conductive	24	5.031-939.0	1 piece(s)	ID 35				Electrically conductive plastic bend (DN 35) with C-35 clip system. For all industrial single-motor NT 361 to NT 611 Eco models.	<input type="checkbox"/>
	25	5.032-427.0	1 piece(s)	ID 40				Electrically conductive plastic bend (DN 40) with C-40 clip system, suitable for all NT vacuum cleaners.	<input type="checkbox"/>
<b>Bends, metal</b>									
Bend, metal	26	6.900-519.0	1 piece(s)	ID 35				Robust, chromium-plated metal bend (DN 35), can be used instead of a plastic bend (with clip system adapter 5.407-112.0; C 35-DN 35, plastic, el.).	<input type="checkbox"/>
	27	6.900-276.0	1 piece(s)	ID 40				Robust, chromium-plated metal bend (DN 40), can be used instead of a plastic bend (with clip system adapter 5.407-111.0; C 40-DN 40, plastic, el.).	<input type="checkbox"/>
<b>All-purpose brushes</b>									
All-purpose brush	28	6.903-863.0	1 piece(s)	ID 35	120 mm			Natural bristles (ox hair), bristle element 120 x 45 mm.	<input type="checkbox"/>
<b>Car cleaning nozzles</b>									
Car nozzle	29	6.900-952.0	1 piece(s)	ID 40		90 mm		Angled, flat, plastic car vacuuming tool with about 90 mm working width. Only for NT vacuum cleaners.	<input type="checkbox"/>
<b>Wide nozzles</b>									
Wide nozzle	30	4.130-432.0	1 piece(s)	ID 40		644 mm		Vacuuming larger Areas in connection with NT 70/1; NT 70/2 or NT 70/3 versions only.	<input type="checkbox"/>
<b>Rubber tool</b>									
Rubber nozzle, ID 40	31	4.763-057.0	1 piece(s)	40				Rubber.	<input type="checkbox"/>
<b>Rubber suction tools, nose 45°</b>									
Rubber suction tool, nose 45°	32	6.902-104.0	1 piece(s)	ID 35	220 mm			45° rubber suction nozzle (DN 35), oil-resistant and suitable for vacuuming machines. Only for NT vacuum cleaners.	<input type="checkbox"/>
	33	6.902-105.0	1 piece(s)	ID 40	220 mm			45° rubber suction nozzle (DN 40), oil-resistant and suitable for vacuuming machines. Only for NT vacuum cleaners.	<input type="checkbox"/>
<b>Radiator brushes</b>									
Heater brush	34	6.903-034.0	1 piece(s)	ID 35				Radiator brush is suitable for crevice tool 6.900-385.0 or 6.905-240.0.	<input type="checkbox"/>
<b>Pipe dusting nozzles</b>									
Pipe brush 35/100	35	6.903-035.0	1 piece(s)	ID 35				Plastic, pipe diameter 100 mm	<input type="checkbox"/>
Pipe brush 35/200	36	6.903-036.0	1 piece(s)	ID 35				Plastic, pipe diameter 200 mm	<input type="checkbox"/>

■ Included in delivery. □ Available accessories.

# ACCESSORIES FOR NT 70/2

## 1.667-277.0

**KÄRCHER**



		Order No.	Quantity	ID	Length	Width	Price	Description	
<b>Suction brushes</b>									
Suction brush	37	6.903-862.0	1 piece(s)	ID 35		70 mm		Rotatable suction brush (DN 35) with natural bristles (cow hair). Bristle size 70x45 mm. Only CV and NT vacuum cleaners.	<input type="checkbox"/>
	38	6.903-887.0	1 piece(s)	ID 32		70 mm		Rotatable suction brush (DN 32 plastic) with PA bristles, 70x45 mm. Only for BV and T vacuum cleaners.	<input type="checkbox"/>
<b>Suction tubes, stainless steel</b>									
Suction tube	39	6.902-081.0	1 piece(s)	ID 40	0.5 m			Stainless steel suction tube (DN 40, 0.5 m) only suitable for NT vacuum cleaners.	<input type="checkbox"/>
	40	6.906-531.0	1 piece(s)	ID 40	1 m			Stainless steel suction tube (DN 40, 1.0 m) only suitable for NT vacuum cleaners.	<input type="checkbox"/>
	41	6.902-154.0	1 piece(s)	ID 35	0.5 m				<input type="checkbox"/>
<b>Repair kits</b>									
Repair kit, C 40	42	2.639-873.0	1 piece(s)	ID 40				Repair set (C40) includes threaded hose adapters (without bayonet adapter) for industrial NT vacuum cleaners with clip system.	<input type="checkbox"/>
Repair kit, DN 61	43	2.862-038.0	1 piece(s)	ID 61				Suction hose repair kit. Optional for all NT 65/2 and 72/2, NT 993 I, NT 802 I.	<input type="checkbox"/>
<b>Suction hoses (clip system)</b>									
Suction hose	44	6.906-279.0	1 piece(s)	40	10 m			10 m standard suction hose without bend and adapter. With bayonet at vacuum end and C 40 clip connection at accessory end.	<input type="checkbox"/>
	45	6.906-321.0	1 piece(s)	40	4 m			4 m suction hose with bayonet and C 40 clip connection. Without bend and adapter.	<input type="checkbox"/>
	46	6.906-546.0	1 piece(s)	40	4 m			Electrically conductive, 4 m suction hose with bayonet and C 40 clip connection. Without bend and adapter.	<input type="checkbox"/>
	47	6.906-635.0	1 piece(s)	40	16 m			With bayonet and clip connection.	<input type="checkbox"/>
	48	6.906-877.0	1 piece(s)	40	10 m			Suction hose with bayonet coupling, electrically conductive.	<input type="checkbox"/>
<b>Suction hoses complete</b>									
Suction hose, complete	49	4.440-264.0	1 piece(s)	ID 61	4 m			4-m standard suction hose with DN 61 bayonet connector at the device end and DN 61 tapered connector at the accessory end.	<input type="checkbox"/>
	50	4.440-328.0	1 piece(s)	ID 61	3 m			Industrial hose, PVC/elastomer with steel spiral, smooth inside	<input type="checkbox"/>
	51	4.440-467.0	1 piece(s)	ID 61	10 m			10-m standard suction hose with DN 61 bayonet connector at the device end and DN 61 tapered connector at the accessory end.	<input type="checkbox"/>
Suction hose, complete, oil-resistant	52	4.440-613.0	1 piece(s)	ID 61	4 m			Oil-resistant.	<input type="checkbox"/>
	53	4.440-614.0	1 piece(s)	ID 61	10 m				<input type="checkbox"/>
Suction hose, complete, electrically conductive	54	4.440-616.0	1 piece(s)	ID 61	4 m			Electrically conductive.	<input type="checkbox"/>
Suction hose, complete	55	4.440-263.0	1 piece(s)	ID 40	4 m			Electrically non-conductive 4.0m standard suction hose with bayonet at vacuum end and DN 40 cone at accessory end.	<input type="checkbox"/>
	56	4.440-303.0	1 piece(s)	ID 40	4 m			Oil-resistant	<input type="checkbox"/>
	57	4.440-463.0	1 piece(s)	ID 40	10 m			Electrically non-conductive 10.0m standard suction hose with bayonet at vacuum end and DN 40 cone at accessory end.	<input type="checkbox"/>
	58	4.440-466.0	1 piece(s)	ID 40	10 m			Electrically conductive, 10.0m, ID 40	<input type="checkbox"/>
Suction hose, complete, oil-resistant	59	4.440-612.0	1 piece(s)	ID 40	10 m			Oil-resistant.	<input type="checkbox"/>

■ Included in delivery. □ Available accessories.



# ACCESSORIES FOR NT 70/2

## 1.667-277.0

**KÄRCHER**


		Order No.	Quantity	ID	Length	Width	Price	Description	
<b>Connecting sleeves</b>									
Connecting adaptor, ID 27, electrically conductive.	60	4.453-006.0	1 piece(s)	ID 27				For connecting 2 suction hoses, thread on both sides, electrically conductive.	<input type="checkbox"/>
Adaptor, ID 32/35, with internal thread	61	6.902-077.0	1 piece(s)	ID 32				Electrically non-conductive adapter with internal thread. For connecting two suction hoses without connectors. Suitable for DN 32 or DN 35.	<input type="checkbox"/>
Connecting adaptor, ID 40, with internal thread	62	6.900-286.0	1 piece(s)	ID 40				Electrically non-conductive adapter with screw thread at both ends. For connecting 2 DN 40 suction hoses without connectors.	<input type="checkbox"/>
Connecting sleeve, ID 61, with female thread	63	6.902-078.0	1 piece(s)	ID 61				For connecting 2 suction hoses, thread on both sides	<input type="checkbox"/>
<b>Extension hoses (clip system)</b>									
Extension hose	64	6.906-344.0	1 piece(s)	ID 40	2.5 m			2.5 m electrically non-conductive standard extension hose for all C-40 hoses with clip system.	<input type="checkbox"/>
<b>Other</b>									
Pre-separator, 80 l	65	3.864-010.0	1 piece(s)						<input type="checkbox"/>
Drum separator	66	3.864-012.0	1 piece(s)						<input type="checkbox"/>
Pre-separator cover	67	4.063-132.0	1 piece(s)						<input type="checkbox"/>
Spacer for 200 l drum	68	6.902-051.0	1 piece(s)						<input type="checkbox"/>
CS 40 Me	69	2.863-026.0	1 piece(s)					The highly efficient CS 40 Me cyclone preseparator for all Kärcher wet and dry vacuum cleaners is a specially designed accessory for fine dust applications on construction sites or in industry.	<input type="checkbox"/>
<b>Y-adaptor kit</b>									
Y-adaptor kit	70	2.637-217.0	1 piece(s)	ID 35				Plastic distributor - suitable for NT vacuum cleaners.	<input type="checkbox"/>
<b>Connection adaptor C ID (clip to cone), electrically conductive</b>									
Connection adaptor C DN 35	71	5.407-112.0	1 piece(s)	ID 35				C 35 hose connector for DN 35 accessory, electrically conductive.	<input type="checkbox"/>
<b>Expansion pieces (tube -&gt; nozzle)</b>									
Adapter	72	5.453-019.0	1 piece(s)	ID 40				From DN 40 to DN 61: Plastic adapter (electrically non-conductive). Suitable for NT vacuum cleaners.	<input type="checkbox"/>
<b>Reducing sleeves</b>									
Reducer	73	5.407-108.0	1 piece(s)	ID 40				Threaded reducer - from C-40 to DN 35. Suitable for NT vacuum cleaners.	<input type="checkbox"/>
Reduction bushing	74	5.407-113.0	1 piece(s)	ID 40				Reducer (C 40 to C 35) for connecting accessories with C-35 clip connection to suction hoses with C 40 clip system.	<input type="checkbox"/>
<b>Reducers (tube -&gt; nozzle)</b>									
Reducer	75	6.902-017.0	1 piece(s)	ID 40				Reducer for accessory extension. Ideal for accessories with DN 35 connecting cone in combination with accessories with DN 40 connecting cone.	<input type="checkbox"/>
Reducer from ID 35 to ID 32	76	6.902-072.0	1 piece(s)	ID 35				Reducer with internal connecting cone DN 32. Ideal for accessories from the industrial vacuum cleaner range in combination with industrial NT vacuum cleaners.	<input type="checkbox"/>
<b>Target-group-specific accessory kits for vacuum cleaners</b>									
Professional cleaning kit	77	2.637-353.0		ID 40				Individual parts: Suction hose 4 m (4.440-263.0), bend, metal (6.900-276.0), suction tube 2 x 0.5 m, metal (6.900-275.0), grout nozzle (6.903-033.0), floor nozzle with rollers (6.903-051.0).	<input type="checkbox"/>
Car cleaning accessory kit	78	2.862-166.0		ID 35				Target group-specific accessory nozzles in DN 35 for interior cleaning of vehicles, upholstery & fixtures.	<input type="checkbox"/>

■ Included in delivery. □ Available accessories.

# ACCESSORIES FOR NT 70/2

## 1.667-277.0



		Order No.	Quantity	ID	Length	Width	Price	Description	
Swarf kit	79	2.640-760.0		ID 61				Target group-specific robust connection set in DN 61 for cleaning in conjunction with oil-resistant suction hose and rubber nozzle.	<input type="checkbox"/>
<b>Coarse dirt filter for wet vacuuming</b>									
Foam filter	80	2.889-083.0	1 piece(s)					Not suitable for dry vacuuming.	<input type="checkbox"/>

■ Included in delivery.    ☐ Available accessories.

# ACCESSORIES FOR NT 70/2

## 1.667-277.0



		Order No.	Length	Colour	Quantity	Price	Description	
Miscellaneous								
Extension cable	1	6.647-022.0	20 m		1 piece(s)		Extension cable, 20 m, 3x1.5 mm <sup>2</sup> . With splash-proof earthing pin plug, strain relief and anti-kink sleeve.	<input type="checkbox"/>

■ Included in delivery.    ☐ Available accessories.



# ACCESSORIES FOR NT 70/2

## 1.667-277.0



		Order No.	Quantity	ID	Length / width	Price	Description	
<b>Other nozzles</b>								
Rubber suction nozzle, 45°	1	6.902-106.0	1 piece(s)	ID 61	220 mm		Angled 45°, for suction of machines, oil-resistant	<input type="checkbox"/>
Scratcher and scraper nozzle, metal	2	6.903-360.0	1 piece(s)	ID 61	104 mm		Scratcher and scraper tool DN 61, sheet metal, 117 mm	<input type="checkbox"/>
Surface nozzle, aluminium	3	4.130-415.0	1 piece(s)	ID 61	200 mm		Flat surface nozzle cpl. DN 51, 200 mm, aluminium with brush and stainless steel bumper	<input type="checkbox"/>

■ Included in delivery.    □ Available accessories.

ACCESSORIES FOR NT 70/2  
1.667-277.0



		Order No.					Price	Description	
Suction hoses									
	1	2.639-905.0						Repair kit for all C-40 and ID 40 hoses	<input type="checkbox"/>

■ Included in delivery.    ☐ Available accessories.