

B1005 - K-Jump/ K-Trek/ K-Rush S1P HRO SRC

Collection: Kaptiv

Upper: Breathable Fabric

Lining: SmellStop Antiodor and Antibacterial*

Midsole: Fresh'n Flex

Toecap: Aluminium

Sole: Double-Density PU/HRO Rubber i-daptive® Technology

Outer Carton: 10

Kaptiv

The first safety footwear range with stability control, designed to offer incredible dynamic comfort.



Standards

UNI EN ISO 20345:2012 S1P (HRO SRC)

Features

- Anti-static footwear
- 200 joules resistant toe-cap
- Puncture resistant sole
- Shock absorption in the heel region
- Heat resistant 1 minute up to 300°C
- Hydrocarbons resistant
- Men's width
- Women's width
- Orthopaedic made to measure footbed, complying with european norms DGUV112-191

PORTWEST®



B1005 - K-Jump/ K-Trek/ K-Rush S1P HRO SRC

Commodity Code: 6404199000

Test House

A.N.C.I. Servizi S.R.L (CIMAC) (Notified Body No.: NB: 0465)
Via Alberto Riva Villasanta, 3
, Italy
Cert No: F-113-00280-18 rev.01

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
B1005GOR39	Grey/Orange	67.0	41.0	36.0	1.2520	0.0989	8054633493489	
B1005GOR40	Grey/Orange	67.0	41.0	36.0	1.3110	0.0989	8054633493496	
B1005GOR41	Grey/Orange	67.0	41.0	36.0	1.3430	0.0989	8054633493502	
B1005GOR42	Grey/Orange	67.0	41.0	36.0	1.4010	0.0989	8054633493519	
B1005GOR43	Grey/Orange	67.0	41.0	36.0	1.4150	0.0989	8054633493526	
B1005GOR44	Grey/Orange	67.0	41.0	36.0	1.5050	0.0989	8054633493533	
B1005GOR45	Grey/Orange	67.0	41.0	36.0	1.5550	0.0989	8054633493540	
B1005GOR46	Grey/Orange	67.0	41.0	36.0	1.6170	0.0989	8054633493557	
B1005GOR47	Grey/Orange	67.0	41.0	36.0	1.6440	0.0989	8054633493564	
B1005GOR48	Grey/Orange	67.0	41.0	36.0	1.7000	0.0989	8054633493571	