

## Han 24HPR EasyCon Cover 1xM40 side entry



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 19 40 024 9927  |
| Specification      | Han 24HPR EasyCon Cover 1xM40 side entry                                      |
| HARTING eCatalogue | <a href="https://harting.com/19400249927">https://harting.com/19400249927</a> |

### Identification

|                             |   |
|-----------------------------|---|
| Category                    | Hoods / Housings                          |
| Series of hoods/housings    | Han <sup>®</sup> HPR EasyCon              |
| Type of hood/housing        | Mounting cover                            |
| Description of hood/housing | for surface mounted housings<br>for hoods |

### Version

|                         |   |
|-------------------------|---|
| Size                    | 24 B  |
| Version                 | Side entry                                    |
| Number of cable entries | 1   |
| Cable entry             | 1x M40  |
| Locking type            | Screw locking                                 |
| Field of application    | Hoods/housings for harsh outdoor environments |

### Technical characteristics

|  |  |
|--|--|
| Tightening torque                      | 6 Nm Mounting cover<br>6 Nm Distance bolt      |
| Limiting temperature                   | -40 ... +125 °C                                |
| Note on the limiting temperature       | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP65<br>IP68<br>IP69 / IPX9K acc. to ISO 20653 |



**Pushing Performance**  
Since 1945

## Technical characteristics

|                                    |    |
|------------------------------------|----|
| Type rating acc. to UL 50 / UL 50E | 4  |
|                                    | 4X |
|                                    | 12 |

## Material properties

|                         |   |
|-------------------------|---|
| Material (hood/housing) | Aluminium die-cast<br>Corrosion resistant |
| Surface (hood/housing)  | Powder-coated                             |
| Colour (hood/housing)   | RAL 9005 (jet black)                      |
| Material (seal)         | NBR                                       |

## Specifications and approvals

|           |  |
|-----------|--|
| UL / CSA  | UL 1977 ECBT2.E235076<br>CSA-C22.2 No. 182.3 ECBT8.E235076 |
| Approvals | DNV GL   |

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 1                                      |
| Net weight                     | 510 g                                  |
| Country of origin              | China                                  |
| European customs tariff number | 85389099                               |
| GTIN                           | 5713140175402                          |
| eCl@ss                         | 27440208 Cap for industrial connectors |
| ETIM                           | EC002314                               |
| UNSPSC 24.0                    | 39121467                               |